


Magnetic field sensor with internal magnet

ZMY20M



package : SOT223S (4-Pin)
 1: +V_O 2: -V_O 3: +V_B 4: -V_B
 V_O - output voltage V_B - supply voltage

FEATURES

- ZMY20M (SOT-223-S) is an extremely sensitive magnetic sensor with internal magnet employing the magneto-resistive effect of thin film permalloy
- Package : SOT-223-S
- The ZMY20M is available on 12 mm tape - 7" reel 1.000 components/reel or 13" reel 4.000 components/reel
- Disturbing fields up to 30 kA/m are allowed
- Internal magnet for creating of the auxiliary field H_X
- Magnetic fields vertical to the chip level are not effective

ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol		Unit
Supply voltage ZMY20M	V _B	12	V
Total power dissipation	P _{tot}	120	mW
Operating temperature range	T _{amb}	-25 to +125	°C
Storage temperature range	T _{stg}	-25 to +125	°C

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25\text{ }^{\circ}\text{C}$ unless otherwise stated)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test conditions
Bridge resistance	R_{br}	1.2	1.7	2.2	$k\Omega$	
Output voltage range	V_O/V_B	12	18	22	mV/V	
Auxiliary field	H_X	-	1.5	-	kA/m	
Disturbing field	H_d	-	-	30	kA/m	
Open circuit sensitivity	S	3.0	5.5	7.0	(mV/V)/(kA/m)	no disturbing field H_d allowed $V_B = \text{const.}$
Hysteresis of output voltage	V_{OH}/V_B	-	-	50	$\mu\text{V/V}$	$H_y \leq 2\text{ kA/m}$
Offset voltage	V_{off}/V_B	-1.5	-	+1.5	mV/V	
Operating frequency	f_{max}	0	-	1	MHz	
Temperature coefficient of offset voltage	TCV_{off}	-3	-	+3	($\mu\text{V/V}$)/K	$T_{amb} = -25\dots+125^{\circ}\text{C}$
Temperature coefficient of bridge resistance	TCR_{br}	-	0.3	-	%/K	$T_{amb} = -25\dots+125^{\circ}\text{C}$
Temperature coefficient of open circuit sensitivity $V_B = 5\text{ V}$	TCS_V	-	-0.25	-	%/K	$T_{amb} = -25\dots+125^{\circ}\text{C}$
Temperature coefficient of open circuit sensitivity $I_B = 3\text{ mA}$	TCS_I	-	0.05	-	%/K	$T_{amb} = -25\dots+125^{\circ}\text{C}$

Devices are identified by type on the body of the device

ZMY20M..... ZMY20M

Ordering information :

ZMY20MTA 7" reel 1,000 components per reel
ZMY20MTC 13" reel 4,000 components per reel

© Zetex plc 2002

Europe

Zetex plc
Fields New Road
Chadderton
Oldham, OL9 8NP
United Kingdom
Telephone (44) 161 622 4422
Fax: (44) 161 622 4420
uk.sales@zetex.com

Zetex GmbH
Streitfeldstraße 19
D-81673 München

Germany
Telefon: (49) 89 45 49 49 0
Fax: (49) 89 45 49 49 49
europe.sales@zetex.com

Americas

Zetex Inc
700 Veterans Memorial Hwy
Hauppauge, NY11788

USA
Telephone: (631) 360 2222
Fax: (631) 360 8222
usa.sales@zetex.com

Asia Pacific

Zetex (Asia) Ltd
3701-04 Metroplaza, Tower 1
Hing Fong Road
Kwai Fong
Hong Kong
Telephone: (852) 26100 611
Fax: (852) 24250 494
asia.sales@zetex.com

These offices are supported by agents and distributors in major countries world-wide.

This publication is issued to provide outline information only which (unless agreed by the Company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the products or services concerned. The Company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.

For the latest product information, log on to www.zetex.com

