

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

(C) COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.



LOC
DYDIST
-

REVISIONS





P	LTR	DESCRIPTION	DATE	DWN	APVD
	0	NPR ECR-05-008261	21JUN05	LWY	SYJ

NOTES:

- 1 SHELLS: BRASS
CONTACTS: PHOSPHOR BRONZE
HOUSING: POLYESTER, UL 94V-O RATED, BLACK
- 2 0.76um [.000030] MIN GOLD ON MATING END FOR A LENGTH OF 1.37[.054] MIN ON INSIDE, 2.540um [.000100] MIN TIN FOR A LENGTH OF 3.30um [.130] MIN FROM OPPOSITE END, ALL OVER 1.27um [.000050] MIN NICKEL.
- 3 2.54um [.000100] MIN TIN OVER 1.27um [.000200] MIN NICKEL OR COPPER.
- 4 3.81um [.000150] MIN TIN OVER 2.54um [.000050] MIN COPPER.
5. RECEPTACLE ASSEMBLY MATES WITH 6 PIN, $\varnothing 8.99 \pm 0.10$ [.354 $\pm$.004] PLUG.



VIEW Z-Z

RECOMMENDED PC BOARD LAYOUT
BOTTOM VIEWPANEL CUT-OUT LAYOUT
SCALE 2:1DETAIL C
SCALE 2:1

4	3	2	5750131-2
OUTER SHELL FINISH	INNER SHELL FINISH	CONTACT FINISH	PART NO.
NAME RECEPTACLE ASSEMBLY, 6 POSITION, LOW FLANGE, SHIELDED, VERTICAL MOUNT, MINIATURE CIRCULAR DIN, LF			
SIZE A3	CAGE CODE 00779	DRAWING NO C-5750131	
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1 REV 0

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	
DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC $\pm$ 1 PLC $\pm$ 2 PLC ± 0.13 [.005] 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$
MATERIAL 	FINISH SEE TABLE

DWN WY LEE	21JUN2005
CHK YJ SEE	
APVD SF L FONG	
PRODUCT SPEC	
APPLICATION SPEC	
WEIGHT	-
CUSTOMER DRAWING	

Tyco Electronics Singapore Pte. Ltd.	
NAME RECEPTACLE ASSEMBLY, 6 POSITION, LOW FLANGE, SHIELDED, VERTICAL MOUNT, MINIATURE CIRCULAR DIN, LF	
SIZE A3	CAGE CODE 00779
DRAWING NO C-5750131	
SCALE 5:1	SHEET 1 OF 1 REV 0