


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		T2	REVISED PER ECO-11-004587	11MAR11	RK	HMR



AMP
WIRE RANGE

8 AWG
SOLID OR STRANDED

- 1

STAMP AMP 8* APPROX AS SHOWN
- 2

UL LISTED E13288, 8 AWG STRANDED
- 3

CSA CERTIFIED LR7189, 8 AWG SOLID OR STRANDED
- 4


MILITARY MS20659-141 CLASS 2
- 5

SUPERSEDED BY 8-33461-1
- 6

TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B545
- 7

TIN-LEAD (60-40) PLATE 0.00254 [.000100] MIN THK PER SAE-AMS-P-81728
- 9

PRELIMINARY - NOT FOR PRODUCTION



OBSOLETE	2 3	6	25	LOOSE PIECE, BAG	8-33461-5
	2 3	6	50	LOOSE PIECE, BOX	9 8-33461-2
	2 3	6	100	LOOSE PIECE, BOX	8-33461-1
	2 3	6	1000	33461 TAPE MOUNTED ON 30.48[1.200] CENTERS	2-33461-3
	2 3 4	6	1500	33461 TAPE MOUNTED ON 15.24[.600] CENTERS	2-33461-2
	---	7	50	LOOSE PIECE	9 33461-1
	2 3 4	6	100	LOOSE PIECE	33461
	APPROVALS	FINISH	QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
N/A

CIRCULAR MIL AREA:
6.64-10.5mm²[13,100-20,800]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
COPPER PER
ASTM B-152
ANNEALED

FINISH
-

DWN
TA BRINKMAN
3-24-93

CHK
DA PATTERSON
3-24-93

APVD
JL MECKLEY
3-24-93

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL, RING TONGUE,
SOLISTRAND

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-33461

RESTRICTED TO
-

SCALE
8:1

SHEET
1 OF 1

REV
T2