







| ▲ SWITCH FUNCTION |        |        |
|-------------------|--------|--------|
| POS. 1            | POS. 2 | POS. 3 |
|                   |        |        |
| ON                | OFF    | ON     |
| 1-2               | OFF    | 2-3    |



CIRCUIT: SPDT  
ON - OFF - ON



RECOMMENDED  
PANEL CUT-OUT



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 16A @ 30VDC, 50/60 Hz,  $\mu$ T85/55  
UL LISTED
5. ELECTRICAL LIFE: 10,000 CYCLES
6. MECHANICAL LIFE: 30,000 CYCLES
7. CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
8. DIELECTRIC STRENGTH: >1,500V AC 1MIN
9. INSULATION RESISTANCE: >100 MOHMS @ 500VDC
10. OPERATING TEMP: 0°C to 55°C
11. LED VOLTAGE: NONE
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT



E-SWITCH®

|     |        |                 |         |    |
|-----|--------|-----------------|---------|----|
| B   | 21355  | Drawing Cleanup | 1/15/14 | rc |
| A   | 21252  | New Release     | 8/14/13 | rc |
| REV | PCR NO | DESCRIPTION     | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE R713FA1-SXXXNB4NNX

SCALE  
1:1DATE  
8/14/2013DR  
rcDWG  
C700005REV  
B