

**Industrial Ethernet
IE-M12-COUP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

M12 panel feed-through, IP67

General ordering data

Type	IE-M12-COUP
Order No.	8901640000
Version	Coupling, M12, M12, Cat.5 (ISO/IEC 11801), IP67
GTIN (EAN)	4032248658206
Qty.	1 pc(s).

Industrial Ethernet IE-M12-COUP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	36 g
------------	------

Temperatures

Operating temperature, max.	60 °C	Operating temperature, min.	-5 °C
Operating temperature	-5 °C...60 °C	Storage temperature	
Installation temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General Info

Connection 1	M12	Connection 2	M12
Description of article	Coupling	Configuration	M12 socket to M12 socket
Housing main material	Polyamide, Brass, nickel-plated	Category	Cat.5 (ISO/IEC 11801)
Connection thread	M12	Shielding	360° shield contact
Protection degree	IP67		

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

Classifications

ETIM 3.0	EC000516	ETIM 4.0	EC000516
ETIM 5.0	EC000516	ETIM 6.0	EC002925
UNSPSC	30-21-18-14	eClass 5.1	27-26-07-02
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	19-17-01-25
eClass 9.1	27-44-03-90		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads


Approval/Certificate/Document of Conformity	GOST Approval PROFINET Manufacturer's Declaration
Brochure/Catalogue	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI PROFINET CABLING EN
Engineering Data	WSCAD
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Industrial Ethernet IE-M12-COUP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing



Dimensioned drawing

