





LOC		DIST		REVISIONS				
GP	00	P	LYR	DESCRIPTION		DATE	DWN	APVD
				B	REVISED PER ECO-10-012356			
				-	-			
				-	-			
				-	-			



- △ HOUSINGS; POLYESTER, UL 94V-O RATED, NATURAL
SIGNAL AND SIGNAL GROUND CONTACTS: COPPER ALLOY
UTILITY CONTACTS: PHOSPHOR BRONZE
- △ UTILITY CONTACTS: 0.76µm MIN GOLD IN CONTACT AREA,
2.54µm MIN TIN-LEAD ON PCB TAILS, OVER 1.27µm MIN NICKEL OVER ALL.
SIGNAL AND SIGNAL GROUND CONTACTS: 0.76µm MIN GOLD IN CONTACT AREA,
2.54µm MIN TIN-LEAD ON PCB TAILS, OVER 1.27µm MIN NICKEL OVER ALL.
3. ROWS A, C, D, AND F ARE SIGNAL CONTACTS. ROWS B AND E ARE SIGNAL GROUND CONTACTS.
- △ CONNECTOR SIZE CAN ACCOMMODATE INDICATED QUANTITY OF DIFFERENTIAL PAIRS.
- △ DIMENSIONS PER CUSTOMER BOARD LAYOUT.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D. RENAUD / D. SINISI.
- △ COMPANY LOGO IN APPROXIMATE AREA SHOWN.



△ 6	OBSOLETE	232	113.44	106.74	88.90	88.39	72	1367680-9
△ 6	OBSOLETE	208	103.28	96.58	78.74	78.23	64	1367680-8
△ 6	OBSOLETE	184	93.12	86.42	68.58	68.07	56	1367680-7
		160	82.96	76.26	58.42	57.91	48	1367680-6
△ 6	OBSOLETE	136	72.80	66.10	48.26	47.75	40	1367680-5
		112	62.64	55.94	38.10	37.59	32	1367680-4
△ 6	OBSOLETE	88	52.48	45.78	27.94	27.43	24	1367680-3
△ 6	OBSOLETE	64	42.32	35.62	17.78	17.27	16	1367680-2
△ 6	OBSOLETE	40	32.16	25.46	7.62	7.11	8	1367680-1
		N	H DIM	D DIM	B DIM	A OR C DIM	DIFF PAIRS △	PART NUMBER

THIS IS A PRELIMINARY DRAWING. IT IS THE USER'S RESPONSIBILITY TO VERIFY THE DIMENSIONS AND TOLERANCES OF THE COMPONENTS AND TO CONTACT THE SUPPLIER FOR THE LATEST REVISION.		DWN N. REESER 26MAY04	Tyco Electronics Harrisburg, PA 17105-3608	
CHK N. REESER 26MAY04		NAME N. REESER	26MAY04	
APVD N. REESER		PRODUCT SPEC 108-1985	APPLICATION SPEC 114-13068	
MATERIAL △		WEIGHT -	CUSTOMER DRAWING	
FINISH △		SCALE 4:1	SHEET 1 OF 1	