

## Low-voltage CMOS quad dual input NAND gate with 5 V tolerant inputs


Datasheet –production data

### Features

- 5 V tolerant inputs
- High speed
  - $t_{PD} = 4.3 \text{ ns (max.)}$  at  $V_{CC} = 3 \text{ V}$
- Power-down protection on inputs and outputs
- Symmetrical output impedance
  - $|I_{OH}| = I_{OL} = 24 \text{ mA (min.)}$  at  $V_{CC} = 3 \text{ V}$
- PCI bus levels guaranteed at 24 mA
- Balanced propagation delay
  - $t_{PLH} \cong t_{PHL}$
- Operating voltage range
  - $V_{CC} \text{ (opr.)} = 2.0 \text{ V to } 3.6 \text{ V}$
- Pin and function compatible with 74 series 00
- Latch-up performance exceeds 500 mA (JESD 17)
- ESD performance
  - HBM: 2000 V (MIL STD 883 method 3015)
  - MM: 200 V
  - CDM: 1000 V

### Applications

- Automotive
- Industrial
- Computer
- Consumer



### Description

The 74LCX00 device is a low-voltage CMOS quad dual input NAND gate manufactured with sub-micron silicon gate and double layer metal wiring C<sup>2</sup>MOS technology. It is ideal for low-power and high-speed 3.3 V applications and can be interfaced to a 5 V signal environment for inputs.

It has the same speed performance at 3.3 V as the 5 V AC/ACT family, combined with lower power consumption.

All inputs and outputs are equipped with protection circuits against static discharge, giving them 2 kV ESD immunity and transient excess voltage.

**Table 1. Device summary**

| Order code                 | Temperature range | Package                    | Packaging     | Marking  |
|----------------------------|-------------------|----------------------------|---------------|----------|
| 74LCX00TTR                 | -40/+85 °C        | TSSOP14                    | Tape and reel | LCX00    |
| 74LCX00YTTR <sup>(1)</sup> | -40/+85 °C        | TSSOP14 (automotive grade) | Tape and reel | LCX00Y   |
| 74LCX00MTR                 | -40/+85 °C        | SO-14                      | Tape and reel | 74LCX00  |
| 74LCX00YMTR <sup>(1)</sup> | -40/+85 °C        | SO-14 (automotive grade)   | Tape and reel | 74LCX00Y |

1. Qualification and characterization according to AEC Q100 and Q003 or equivalent, advanced screening according to AEC Q001 and Q002 or equivalent.

Contents

1      **Logic symbols and I/O equivalent circuit** ..... 3

2      **Pin settings** ..... 4

      2.1    Pin connections ..... 4

      2.2    Pin description ..... 4

      2.3    Truth table ..... 4

3      **Maximum ratings** ..... 5

      Recommended operating conditions ..... 5

4      **Electrical characteristics** ..... 6

5      **Test circuit** ..... 8

6      **Waveforms** ..... 9

7      **Package mechanical data** ..... 10

8      **Revision history** ..... 15



# 1 Logic symbols and I/O equivalent circuit

Figure 1. IEC logic symbols






Figure 2. Input and output equivalent circuit



## 2 Pin settings

### 2.1 Pin connections

Figure 3. Pin connections (top through view)



### 2.2 Pin description

Table 2. Pin description

| Pin number   | Symbol          | Name and function       |
|--------------|-----------------|-------------------------|
| 1, 4, 9, 12  | 1A to 4A        | Data inputs             |
| 2, 5, 10, 13 | 1B to 4B        | Data inputs             |
| 3, 6, 8, 11  | 1Y to 4Y        | Data outputs            |
| 7            | GND             | Ground (0 V)            |
| 14           | V <sub>CC</sub> | Positive supply voltage |

### 2.3 Truth table

Table 3. Truth table

| Inputs |   | Output |
|--------|---|--------|
| A      | B | Y      |
| L      | L | H      |
| L      | H | H      |
| H      | L | H      |
| H      | H | L      |

### 3 Maximum ratings

Stressing the device above the rating listed in [Table 4: Absolute maximum ratings](#) may cause permanent damage to the device. These are stress ratings only and operation of the device at these or any other conditions above those indicated in [Table 5: Recommended operating conditions](#) of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

**Table 4. Absolute maximum ratings**

| Symbol    | Parameter                                            | Value                  | Unit |
|-----------|------------------------------------------------------|------------------------|------|
| $V_{CC}$  | Supply voltage                                       | -0.5 to +7.0           | V    |
| $V_I$     | DC input voltage                                     | -0.5 to +7.0           | V    |
| $V_O$     | DC output voltage ( $V_{CC} = 0$ V)                  | -0.5 to +7.0           | V    |
| $V_O$     | DC output voltage (high or low state) <sup>(1)</sup> | -0.5 to $V_{CC} + 0.5$ | V    |
| $I_{IK}$  | DC input diode current                               | -50                    | mA   |
| $I_{OK}$  | DC output diode current <sup>(2)</sup>               | -50                    | mA   |
| $I_O$     | DC output current                                    | $\pm 50$               | mA   |
| $I_{CC}$  | DC supply current per supply pin                     | $\pm 100$              | mA   |
| $I_{GND}$ | DC ground current per supply pin                     | $\pm 100$              | mA   |
| $T_{stg}$ | Storage temperature                                  | -65 to +150            | °C   |
| $T_L$     | Lead temperature (10 sec.)                           | 300                    | °C   |

1.  $I_O$  absolute maximum rating must be observed.

2.  $V_O < GND$ .

### Recommended operating conditions

**Table 5. Recommended operating conditions**

| Symbol           | Parameter                                                   | Value         | Unit |
|------------------|-------------------------------------------------------------|---------------|------|
| $V_{CC}$         | Supply voltage <sup>(1)</sup>                               | 2.0 to 3.6    | V    |
| $V_I$            | Input voltage                                               | 0 to 5.5      | V    |
| $V_O$            | Output voltage ( $V_{CC} = 0$ V)                            | 0 to 5.5      | V    |
| $V_O$            | Output voltage (high or low state)                          | 0 to $V_{CC}$ | V    |
| $I_{OH}, I_{OL}$ | High or low level output current ( $V_{CC} = 3.0$ to 3.6 V) | $\pm 24$      | mA   |
| $I_{OH}, I_{OL}$ | High or low level output current ( $V_{CC} = 2.7$ V)        | $\pm 12$      | mA   |
| dt/dv            | Input rise and fall time <sup>(2)</sup>                     | 0 to 10       | ns/V |

1. Truth table guaranteed: 1.5 V to 3.6 V.

2.  $V_{IN}$  from 0.8 V to 2 V at  $V_{CC} = 3.0$  V.

## 4 Electrical characteristics

**Table 6. DC specifications**

| Symbol           | Parameter                       | Test condition         |                                                 | Value                 |      | Unit |
|------------------|---------------------------------|------------------------|-------------------------------------------------|-----------------------|------|------|
|                  |                                 | V <sub>CC</sub><br>(V) |                                                 | -40 to 85 °C          |      |      |
|                  |                                 |                        |                                                 | Min.                  | Max. |      |
| V <sub>IH</sub>  | High level input voltage        | 2.7 to 3.6             |                                                 | 2.0                   |      | V    |
| V <sub>IL</sub>  | Low level input voltage         |                        |                                                 |                       | 0.8  | V    |
| V <sub>OH</sub>  | High level output voltage       | 2.7 to 3.6             | I <sub>O</sub> = -100 μA                        | V <sub>CC</sub> - 0.2 |      | V    |
|                  |                                 | 2.7                    | I <sub>O</sub> = -12 mA                         | 2.2                   |      |      |
|                  |                                 | 3.0                    | I <sub>O</sub> = -18 mA                         | 2.4                   |      |      |
|                  |                                 |                        | I <sub>O</sub> = -24 mA                         | 2.2                   |      |      |
| V <sub>OL</sub>  | Low level output voltage        | 2.7 to 3.6             | I <sub>O</sub> = 100 μA                         |                       | 0.2  | V    |
|                  |                                 | 2.7                    | I <sub>O</sub> = 12 mA                          |                       | 0.4  |      |
|                  |                                 | 3.0                    | I <sub>O</sub> = 16 mA                          |                       | 0.4  |      |
|                  |                                 |                        | I <sub>O</sub> = 24 mA                          |                       | 0.55 |      |
| I <sub>I</sub>   | Input leakage current           | 2.7 to 3.6             | V <sub>I</sub> = 0 to 5.5 V                     |                       | ±5   | μA   |
| I <sub>off</sub> | Power OFF leakage current       | 0                      | V <sub>I</sub> or V <sub>O</sub> = 5.5 V        |                       | 10   | μA   |
| I <sub>CC</sub>  | Quiescent supply current        | 2.7 to 3.6             | V <sub>I</sub> = V <sub>CC</sub> or GND         |                       | 10   | μA   |
|                  |                                 |                        | V <sub>I</sub> or V <sub>O</sub> = 3.6 to 5.5 V |                       | ± 10 |      |
| ΔI <sub>CC</sub> | I <sub>CC</sub> incr. per input | 2.7 to 3.6             | V <sub>IH</sub> = V <sub>CC</sub> - 0.6 V       |                       | 500  | μA   |

**Table 7. Dynamic switching characteristics**

| Symbol           | Parameter                                        | Test condition         |                                                                          | Value                  |      |      | Unit |
|------------------|--------------------------------------------------|------------------------|--------------------------------------------------------------------------|------------------------|------|------|------|
|                  |                                                  | V <sub>CC</sub><br>(V) |                                                                          | T <sub>A</sub> = 25 °C |      |      |      |
|                  |                                                  |                        |                                                                          | Min.                   | Typ. | Max. |      |
| V <sub>OLP</sub> | Dynamic low level<br>quiet output <sup>(1)</sup> | 3.3                    | C <sub>L</sub> = 50 pF<br>V <sub>IL</sub> = 0 V, V <sub>IH</sub> = 3.3 V |                        | 0.8  |      | V    |
| V <sub>OLV</sub> |                                                  |                        |                                                                          |                        | -0.8 |      |      |

1. Number of outputs defined as "n". Measured with "n-1" outputs switching from HIGH to LOW or LOW to HIGH. The remaining output is measured in the LOW state.

**Table 8. AC electrical characteristics**

| Symbol                                 | Parameter                                      | Test condition         |                        |                       |                                         | Value        |      | Unit |
|----------------------------------------|------------------------------------------------|------------------------|------------------------|-----------------------|-----------------------------------------|--------------|------|------|
|                                        |                                                | V <sub>CC</sub><br>(V) | C <sub>L</sub><br>(pF) | R <sub>L</sub><br>(Ω) | t <sub>s</sub> = t <sub>r</sub><br>(ns) | -40 to 85 °C |      |      |
|                                        |                                                |                        |                        |                       |                                         | Min.         | Max. |      |
| t <sub>PLH</sub> t <sub>PHL</sub>      | Propagation delay time                         | 2.7                    | 50                     | 500                   | 2.5                                     |              | 5.1  | ns   |
|                                        |                                                | 3.0 to 3.6             |                        |                       |                                         | 1.0          | 4.3  |      |
| t <sub>OSLH</sub><br>t <sub>OSHL</sub> | Output-to-output skew time <sup>(1), (2)</sup> | 3.0 to 3.6             | 50                     | 500                   | 2.5                                     |              | 1.0  | ns   |

1. Skew is defined as the absolute value of the difference between the actual propagation delay for any two outputs of the same device switching in the same direction, either HIGH or LOW (t<sub>OSLH</sub> = |t<sub>PLHm</sub> - t<sub>PLHn</sub>|, t<sub>OSHL</sub> = |t<sub>PLHm</sub> - t<sub>PLHn</sub>|).
2. Parameter guaranteed by design.


**Table 9. Capacitive characteristics**

| Symbol          | Parameter                                    | Test condition         |                                                                    | Value                  |      |      | Unit |
|-----------------|----------------------------------------------|------------------------|--------------------------------------------------------------------|------------------------|------|------|------|
|                 |                                              | V <sub>CC</sub><br>(V) |                                                                    | T <sub>A</sub> = 25 °C |      |      |      |
|                 |                                              |                        |                                                                    | Min.                   | Typ. | Max. |      |
| C <sub>IN</sub> | Input capacitance                            | 3.3                    | V <sub>IN</sub> = 0 to V <sub>CC</sub>                             |                        | 6    |      | pF   |
| C <sub>PD</sub> | Power dissipation capacitance <sup>(1)</sup> | 3.3                    | f <sub>IN</sub> = 10 MHz<br>V <sub>IN</sub> = 0 or V <sub>CC</sub> |                        | 35   |      | pF   |

1. C<sub>PD</sub> is defined as the value of the IC's internal equivalent capacitance which is calculated from the operating current consumption without load. (Refer to [Section 5: Test circuit](#)). Average operating current can be obtained by the following equation. I<sub>CC(opr)</sub> = C<sub>PD</sub> × V<sub>CC</sub> × f<sub>IN</sub> + I<sub>CC</sub>/4 (per gate).

## 5 Test circuit

Figure 4. Test circuit




Note:

- $C_L = 50 \text{ pF}$  or equivalent (includes jig and probe capacitance)
- $R_L = 500 \Omega$  or equivalent
- $R_T = Z_{OUT}$  of pulse generator (typically  $50 \Omega$ ).

## 6 Waveforms

Figure 5. Waveform - propagation delay ( $f = 1\text{ MHz}$ ; 50% duty cycle)



## 7 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK is an ST trademark.

Figure 6. SO-14 package outline




Table 10. SO-14 package mechanical data

| Symbol | Dimensions |      |       |       |       |       |
|--------|------------|------|-------|-------|-------|-------|
|        | mm         |      |       | inch  |       |       |
|        | Min.       | Typ. | Max.  | Min.  | Typ.  | Max.  |
| A      | 1.35       |      | 1.75  | 0.053 |       | 0.069 |
| A1     | 0.1        |      | 0.25  | 0.004 |       | 0.010 |
| A2     | 1.10       |      | 1.65  | 0.043 |       | 0.065 |
| B      | 0.33       |      | 0.51  | 0.013 |       | 0.020 |
| C      | 0.19       |      | 0.25  | 0.007 |       | 0.010 |
| D      | 8.55       |      | 8.75  | 0.337 |       | 0.344 |
| E      | 3.8        |      | 4.0   | 0.150 |       | 0.157 |
| e      |            | 1.27 |       |       | 0.050 |       |
| H      | 5.8        |      | 6.2   | 0.228 |       | 0.244 |
| h      | 0.25       |      | 0.50  | 0.010 |       | 0.020 |
| L      | 0.4        |      | 1.27  | 0.016 |       | 0.050 |
| k      | 0°         |      | 8°    | 0°    |       | 8°    |
| ddd    |            |      | 0.100 |       |       | 0.004 |

Figure 7. TSSOP14 package outline





Table 11. TSSOP14 package mechanical data

| Symbol | Dimensions |          |      |       |            |        |
|--------|------------|----------|------|-------|------------|--------|
|        | mm         |          |      | inch  |            |        |
|        | Min.       | Typ.     | Max. | Min.  | Typ.       | Max.   |
| A      |            |          | 1.2  |       |            | 0.047  |
| A1     | 0.05       |          | 0.15 | 0.002 | 0.004      | 0.006  |
| A2     | 0.8        | 1        | 1.05 | 0.031 | 0.039      | 0.041  |
| b      | 0.19       |          | 0.30 | 0.007 |            | 0.012  |
| c      | 0.09       |          | 0.20 | 0.004 |            | 0.0089 |
| D      | 4.9        | 5        | 5.1  | 0.193 | 0.197      | 0.201  |
| E      | 6.2        | 6.4      | 6.6  | 0.244 | 0.252      | 0.260  |
| E1     | 4.3        | 4.4      | 4.48 | 0.169 | 0.173      | 0.176  |
| e      |            | 0.65 BSC |      |       | 0.0256 BSC |        |
| K      | 0°         |          | 8°   | 0°    |            | 8°     |
| L      | 0.45       | 0.60     | 0.75 | 0.018 | 0.024      | 0.030  |


Figure 8. Tape and reel SO-14 outline



1. Drawing is not in scale.

Table 12. Tape and reel SO-14 mechanical data

| Symbol | Dimensions |      |      |       |      |        |
|--------|------------|------|------|-------|------|--------|
|        | mm         |      |      | inch  |      |        |
|        | Min.       | Typ. | Max. | Min.  | Typ. | Max.   |
| A      |            |      | 330  |       |      | 12.992 |
| C      | 12.8       |      | 13.2 | 0.504 |      | 0.519  |
| D      | 20.2       |      |      | 0.795 |      |        |
| N      | 60         |      |      | 2.362 |      |        |
| T      |            |      | 22.4 |       |      | 0.882  |
| Ao     | 6.4        |      | 6.6  | 0.252 |      | 0.260  |
| Bo     | 9          |      | 9.2  | 0.354 |      | 0.362  |
| Ko     | 2.1        |      | 2.3  | 0.082 |      | 0.090  |
| Po     | 3.9        |      | 4.1  | 0.153 |      | 0.161  |
| P      | 7.9        |      | 8.1  | 0.311 |      | 0.319  |

**Figure 9. Tape and reel TSSOP14 outline**

Drawing is not in scale.

**Table 13. Tape and reel TSSOP14 mechanical data**

| Symbol | Dimensions |      |      |       |      |        |
|--------|------------|------|------|-------|------|--------|
|        | mm         |      |      | inch  |      |        |
|        | Min.       | Typ. | Max. | Min.  | Typ. | Max.   |
| A      |            |      | 330  |       |      | 12.992 |
| C      | 12.8       |      | 13.2 | 0.504 |      | 0.519  |
| D      | 20.2       |      |      | 0.795 |      |        |
| N      | 60         |      |      | 2.362 |      |        |
| T      |            |      | 22.4 |       |      | 0.882  |
| Ao     | 6.7        |      | 6.9  | 0.264 |      | 0.272  |
| Bo     | 5.3        |      | 5.5  | 0.209 |      | 0.217  |
| Ko     | 1.6        |      | 1.8  | 0.063 |      | 0.071  |
| Po     | 3.9        |      | 4.1  | 0.153 |      | 0.161  |
| P      | 7.9        |      | 8.1  | 0.311 |      | 0.319  |

## 8 Revision history

**Table 14. Document revision history**

| Date        | Revision | Changes                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|-------------|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 15-Sep-2004 | 4        | Ordering code revision - pag 1                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| 07-Jul-2006 | 5        | New template, temperature ranges updated                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| 20-Jun-2012 | 6        | Added <a href="#">Applications on page 1</a><br>Updated <a href="#">Table 1: Device summary on page 1</a><br>Updated T <sub>op</sub> in <a href="#">Table 5: Recommended operating conditions</a><br>Updated ECOPACK® text in <a href="#">Section 7: Package mechanical data</a><br>Minor textual updates                                                                                                                                                                       |
| 02-Oct-2012 | 7        | Updated ESD performance in <a href="#">Features</a> (updated HBM and MM, added CDM).<br>Added 74LCX00YMTR device and "Marking" to <a href="#">Table 1</a> , updated temperature range, note <a href="#">1</a> .<br>Updated <a href="#">Section 3: Maximum ratings</a> (added cross-references).<br>Removed "Operating temperature" from <a href="#">Table 5</a> .<br>Reformatted <a href="#">Section 7: Package mechanical data</a> .<br>Minor corrections throughout document. |

**Please Read Carefully:**

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

**UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.**

**UNLESS EXPRESSLY APPROVED IN WRITING BY TWO AUTHORIZED ST REPRESENTATIVES, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.**

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2012 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

[www.st.com](http://www.st.com)