

10		9		8		7
CONNECTOR P/N	ØD (µm)	CONNECTOR BODY COLOR	BOOT COLOR	CABLE Ø (mm)	CABLE TYPE	
106025-2400	125.50	BLUE	WHITE	1.6	SINGLE MODE	
106025-2600				2.0		
106025-3400	127.00	BEIGE		1.6	MULTIMODE	
106025-3600				2.0		
106025-4400	125.00	BLUE		1.6	SINGLE MODE	
106025-4600				2.0		
106025-5400	1.6					
106025-5600	2.0					
106025-6400	1.6					
106025-6600	2.0					

F

E

D

C

B

A

NOTES:

1. DUPLEX CLIP AND BOOTS SHOULD BE ASSEMBLED AFTER POLISHING OPERATION.

9

8

7

6



5

4


3

2

1



VIEW A



FIBER OPTIC CABLE

ENTER DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: MF2013-0244		DRAWN BY: DRINKPEVZNER		DATE: 2012/10/30		IN/MM		4:1		INCH			
CHKD: CHKD		APPR: LGUMIN		DATE: 2012/10/31		DRAWN BY: PGIBLIN		DATE: 2005/09/07		TITLE: LC DUPLEX CONNECTOR (90D BOOT)			
						CHECKED BY:		DATE:					
						APPROVED BY:		DATE:					
						MATERIAL NO.		DOCUMENT NO.					
						SEE TABLE		SD-1060EE-EEEE0					
						SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

ANGULAR ±1/2°
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

SEE TABLE

SHEET NO.
1 OF 1