

Distributed by:

JAMECO[®]
ELECTRONICS



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 300557

Date	Rev.	Description

Size : 80 x 80 x 25
Unit : mm



Terminal or Lead Wire Type

Impedance Protection

Spec. Model	Rated Voltage V	Frequency Hz	Input Power W	Rated Current A	Locked Current A	Speed RPM	Maximum Air Flow m ³ /min.	Maximum Air Flow CFM	Maximum Pressure mmH ₂ O	Maximum Pressure InchH ₂ O	Noise dB	Weight kg
UF80B10-H	100V	50	16	0.19	0.20	2600	0.59	21	4.0	0.16	32	0.26
		60	14	0.18	0.19	3100	0.68	24	5.5	0.22	35	
UF80B11-H	115V	50	14	0.15	0.16	2600	0.59	21	4.0	0.16	32	0.26
		60	11	0.12	0.13	3100	0.68	24	5.5	0.22	35	
UF80B20-H	200V	50	16	0.08	0.09	2600	0.59	21	4.0	0.16	32	0.26
		60	14	0.07	0.08	3100	0.68	24	5.5	0.22	35	
UF80B23-H	230V	50	16	0.08	0.09	2600	0.59	21	4.0	0.16	32	0.26
		60	14	0.07	0.08	3100	0.68	24	5.5	0.22	35	
UF80B11-L	115V	50	14	0.14	0.15	1900	0.40	15	2.0	0.08	28	0.26
		60	11	0.12	0.13	2400	0.50	18	3.5	0.14	31	
UF80B23-L	230V	50	16	0.07	0.08	1900	0.40	15	2.0	0.08	28	0.26
		60	14	0.06	0.07	2400	0.50	18	3.5	0.14	31	

DCC. NO.
A4 DRAWING NO.

MATERIAL			GOLDSUN ELECTRONICS CO., LTD.			
			JAMECO NO. 300557		GOLDSUN NO. UF80B11-H	
DRWN	Kiki Chen	DATE	Description FAN			Rev. 1
CHK	Ada Zheng	DATE	UNIT: mm			
APVD	Chesley Chang	DATE	SCALE:		SHEET 1 OF 1	CAS No: ERN No: