




Miniature Aluminum Electrolytic Capacitors

XRL Series

FEATURES

- Low impedance characteristics
- Case sizes are smaller than conventional general-purpose capacitors, with very high performance
- Can size larger than 9mm diameter has safety vents on rubber end seal



CHARACTERISTICS

Item	Characteristics													
Operating Temperature Range	-40°C ~ +85°C													
Capacitance Tolerance	±20% at 120Hz, 20°C													
Leakage Current	≤100V	I = 0.01CWV or 3μA whichever is greater after 2 minutes of applied rated DC working voltage at 20°C Where: C = rated capacitance in μF; WV = rated DC working voltage												
	>100V	CWV ≤ 1000 μF: I= 0.03 CWV + 15uA; C= rated capacitance in uF CWV ≥ 1000 μF: I= 0.02 CWV + 25uA; WV= rated DC working voltage in V												
Dissipation Factor (Tan δ, at 20°C 120Hz)	Working voltage (WV)	6.3	10	16	25	35	50	63	100	160	250	350	450	
	Tan δ	0.23	0.20	0.16	0.14	0.12	0.10	0.09	0.08	0.12	0.17	0.20	0.25	
	For capacitors whose capacitance exceeds 1,000μF, the specification of tan δ is increased by 0.02 for every addition of 1,000μF													
Surge Voltage	Working voltage (WV)	6.3	10	16	25	35	50	63	100	160	250	350	450	
	Surge voltage (SV)	8	13	20	32	44	63	79	125	200	300	400	500	
Low Temperature Characteristics (Imp. ratio @ 120Hz)	Working voltage (WV)	6.3	10	16	25	35	50	63	100	160	250	350	450	
	Z(-25°C)/Z(+20°C)	øD<16	6	4	3	3	2	2	2	2	3	8	12	16
		øD≥16	8	6	4	4	3	3	3	3	3	8	12	16
	Z(-40°C)/Z(+20°C)	øD<16	10	8	6	6	4	3	3	3	4	8	16	20
		øD≥16	18	16	12	10	8	8	6	6	4	8	16	20
Load Test	When returned to +20°C after 2,000 hours application of working voltage at +85°C, the capacitor will meet the following limits: Capacitance change is ≤ ±20% of initial value; tan δ is < 200% of specified value; leakage current is within specified value													
Shelf Life Test	When returned to +20°C after 1,000 hours at +85°C with no voltage applied, the capacitor will meet the following limits: Capacitance change is ≤ ±20% of initial value; tan δ is < 200% of specified value; leakage current is within specified value													

PART NUMBERING SYSTEM

X	R	L	1	6	V	1	0	0
Series			Voltage Actual Value			Capacitance (μF) Actual Value		

RIPPLE CURRENT AND FREQUENCY MULTIPLIERS

Capacitance (μF)	Frequency (Hz)				
	60 (50)	120	500	1K	≥10K
<100	0.70	1.0	1.30	1.40	1.50
100 ~ 1000	0.75	1.0	1.20	1.30	1.35
>1000	0.80	1.0	1.10	1.12	1.15

RIPPLE CURRENT AND TEMPERATURE MULTIPLIERS

Temperature (°C)	<50	70	85
Multiplier	1.78	1.4	1.0



XICON PASSIVE COMPONENTS • (800) 628-0544

XC-600030

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.


Date Revised: 9/30/05



Miniature Aluminum Electrolytic Capacitors

XRL Series

■ DIMENSIONS AND PERMISSIBLE RIPPLE CURRENT



Lead Spacing and Diameter (mm)

φD	5	6.3	8	10	13	16	18	22	25
P	2.0	2.5	3.5	5.0	5.0	7.5	7.5	10	12.5
φd	0.5	0.5	0.6	0.6	0.6	0.8	0.8	1.0	1.0

Tape and box is 5.0mm lead space.

Value (μF)	Working Voltage (WV); Dimensions: φD x L (mm); Ripple Current: mA/RMS @ 120Hz, 85°C													
	10		16		25		35		50		63		100	
	φD x L	mA	φD x L	mA	φD x L	mA	φD x L	mA	φD x L	mA	φD x L	mA	φD x L	mA
.10									5 x 11	1.5	5 x 11	3.0	5 x 11	3.0
.22									5 x 11	3.5	5 x 11	4.5	5 x 11	5.8
.33									5 x 11	5.0	5 x 11	7.5	5 x 11	8.8
.47					5 x 11	6.0			5 x 11	7.0	5 x 11	9.5	5 x 11	12
1.0					5 x 11	10			5 x 11	15	5 x 11	17	5 x 11	22
2.2			5 x 11	20	5 x 11	16			5 x 11	29	5 x 11	28	5 x 11	33
3.3			5 x 11	30	5 x 11	25			5 x 11	35	5 x 11	34	5 x 11	40
4.7			5 x 11	41	5 x 11	31	5 x 11	40	5 x 11	42	5 x 11	45	5 x 11	48
10	5 x 11	54	5 x 11	49	5 x 11	54	5 x 11	58	5 x 11	65	5 x 11	70	6.3 x 11	80
22	5 x 11	70	5 x 11	75	5 x 11	80	5 x 11	87	5 x 11	95	6.3 x 11	115	8 x 11.5	135
33	5 x 11	84	5 x 11	90	5 x 11	97	6.3 x 11	115	6.3 x 11	136	8 x 11.5	150	10 x 16	195
47	5 x 11	100	5 x 11	110	5 x 11	115	6.3 x 11	145	6.3 x 11	165	8 x 11.5	190	10 x 16	255
100	5 x 11	145	6.3 x 11	180	6.3 x 11	190	8 x 11.5	240	8 x 11.5	260	10 x 12	320	10 x 20	370
220	6.3 x 11	250	8 x 11.5	300	8 x 11.5	320	10 x 12	420	10 x 16	490	10 x 20	565	13 x 25	675
330	8 x 11.5	350	8 x 11.5	370	10 x 12.5	470	10 x 16	570	13 x 20	635	13 x 20	765	16 x 32	972
470	8 x 11.5	415	10 x 12.5	520	10 x 16	620	10 x 16	740	13 x 20	860	16 x 25	1050	18 x 36	1135
1000	10 x 12.5	650	10 x 16	785	13 x 20	1090	13 x 20	1145	16 x 25	1530	16 x 25	1700	22 x 40	2600
2200	13 x 20	1240	13 x 20	1295	16 x 25	1660	16 x 32	1890	18 x 40	2231	18 x 40	2385		
3300	13 x 20	1420	16 x 25	1840	16 x 32	2070	18 x 36	2430	22 x 40	2785	22 x 40	3000		
4700	16 x 25	1980	16 x 32	2260	18 x 36	2520	18 x 36	2700	25 x 40	3300	25 x 40	3560		
6800	16 x 25	2220	16 x 32	2520	18 x 36	2880	22 x 41	2900						
10000	18 x 40	2880	18 x 40	3080	22 x 40	3440								

Value (μF)	Working Voltage (WV); Dimensions: φD x L (mm); Ripple Current: mA/RMS @ 120Hz, 85°C							
	160		250		350		450	
	φD x L	mA	φD x L	mA	φD x L	mA	φD x L	mA
.47	5 x 11	13	8 x 11.5	21	8 x 11.5	21	10 x 12.5	26
1.0	5 x 11	20	8 x 11.5	32	8 x 11.5	32	10 x 12.5	38
2.2	6.3 x 11	34	8 x 11.5	49	10 x 16	63	10 x 16	63
3.3	8 x 11.5	50	10 x 12.5	70	10 x 16	78	10 x 20	86
4.7	8 x 11.5	60	10 x 16	93	10 x 20	103	13 x 20	120
10	10 x 16	115	10 x 20	150	13 x 20	174	13 x 25	192
22	13 x 20	216	13 x 20	255	13 x 25	282	16 x 25	354
33	13 x 20	270	13 x 25	348	16 x 32	438	18 x 36	490
47	13 x 25	354	16 x 25	468	16 x 36	500	18 x 40	600
100	16 x 25	582	18 x 40	822	18 x 40	685	22 x 45	750
220	18 x 36	900	22 x 40	1134				
330	22 x 40	1010						







Miniature Aluminum Electrolytic Capacitors

XRL Series

TYPICAL PERFORMANCE CHARACTERISTICS

----- 1000 μ F 16V
———— 1 μ F 50V



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

[140-XRL100V10-TB](#) [140-XRL35V4700](#) [140-XRL25V4700](#) [140-XRL50V0.47-TB](#) [140-XRL63V68](#) [140-XRL63V10](#)
[140-XRL50V2.2-TB](#) [140-XRL350V2.2-TB](#) [140-XRL50V470-TB](#) [140-XRL10V10](#) [140-XRL250V3.3-TB](#) [140-](#)
[XRL100V0.47-TB](#) [140-XRL63V6.8-TB](#) [140-XRL50V330-TB](#) [140-XRL25V10](#) [140-XRL25V47](#) [140-XRL35V470](#) [140-](#)
[XRL25V.47-TB](#) [140-XRL35V680](#) [140-XRL160V22-TB](#) [140-XRL100V22-TB](#) [140-XRL25V470](#) [140-XRL10V220](#) [140-](#)
[XRL50V1.0-TB](#) [140-XRL16V6800](#) [140-XRL63V220](#) [140-XRL350V22-TB](#) [140-XRL16V3.3-TB](#) [140-XRL25V4.7-TB](#)
[140-XRL10V3300-TB](#) [140-XRL450V10](#) [140-XRL450V22](#) [140-XRL10V10-TB](#) [140-XRL35V10-TB](#) [140-XRL25V10-TB](#)
[140-XRL50V10-TB](#) [140-XRL63V10-TB](#) [140-XRL250V6.8-TB](#) [140-XRL63V100-TB](#) [140-XRL63V2.2](#) [140-XRL50V15-](#)
[TB](#) [140-XRL350V3.3](#) [140-XRL63V4.7](#) [140-XRL250V3.3](#) [140-XRL16V4.7-TB](#) [140-XRL16V330](#) [140-XRL16V22](#) [140-](#)
[XRL16V3.3](#) [140-XRL100V1000](#) [140-XRL250V2.2-TB](#) [140-XRL16V47](#) [140-XRL16V10](#) [140-XRL50V4.7-TB](#) [140-](#)
[XRL63V100](#) [140-XRL16V2.2-TB](#) [140-XRL16V470-TB](#) [140-XRL10V470-TB](#) [140-XRL63V47](#) [140-XRL450V2.2](#) [140-](#)
[XRL350V2.2](#) [140-XRL25V1.0](#) [140-XRL100V22](#) [140-XRL50V470](#) [140-XRL50V4700](#) [140-XRL10V4700](#) [140-](#)
[XRL35V4.7-TB](#) [140-XRL10V100](#) [140-XRL35V3300](#) [140-XRL25V3300](#) [140-XRL25V220-TB](#) [140-XRL100V3.3-TB](#)
[140-XRL250V4.7](#) [140-XRL450V4.7](#) [140-XRL25V1.0-TB](#) [140-XRL450V2.2-TB](#) [140-XRL35V470-TB](#) [140-XRL35V4.7](#)
[140-XRL160V47-TB](#) [140-XRL100V47-TB](#) [140-XRL50V3.3-TB](#) [140-XRL16V470](#) [140-XRL100V220-TB](#) [140-](#)
[XRL16V4.7](#) [140-XRL35V220-TB](#) [140-XRL50V220-TB](#) [140-XRL35V1000-TB](#) [140-XRL450V3.3-TB](#) [140-XRL25V10000](#)
[140-XRL16V10000](#) [140-XRL10V10000](#) [140-XRL250V10-TB](#) [140-XRL50V1000](#) [140-XRL10V1000](#) [140-XRL450V10-](#)
[TB](#) [140-XRL100V2.2-TB](#) [140-XRL10V220-TB](#) [140-XRL16V220-TB](#) [140-XRL16V330-TB](#) [140-XRL35V6800](#) [140-](#)
[XRL25V6800](#)