



MOD	LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
4	BD	39				E	ADDED -3 PER NPR 4680 AND REDRAWN ON CAD	04/07/93	-
						E1	REVISED PER ECO-09-020935	09SEP09	KK AEG



TAPE MTG DETAIL
SCALE 2:1

1. 0.76μm [.000030] MIN GOLD OVER 1.27μm [.000050] MIN NICKEL.
2. PLATING THICKNESS TO BE MEASURED ON SURFACES ACCESSIBLE WITH 0.64 [.025] DIA SPHERE.
3. WHEN ORDERING CONTACT ASSEMBLY ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
- FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL—
 - 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
 - FOR USE WITH 4/8 INDENT STRIPPER CRIMPER—
 - 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
 - 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL

4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4 OBSOLETE	SMALL PACK	202508-3
4 OBSOLETE	TAPE MTG (SEE DETAIL) 3	202508-2
	STANDARD	202508-1

PACKAGING TYPE			PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON :	DR 04/07/93 D.GELTZ	AMP AMP Incorporated Harrisburg, PA 17105-3608	
2 PLC DEC ± -	CHK 4-26-93 R.STONE		
3 PLC DEC ± -	APPD 4-29-93 R.S.KLINE		
ANGLES ± -	APPD -	CONTACT ASSEMBLY, SOCKET, #16, 16-18 AWG, TYPE II	
MATERIAL	PRODUCT SPEC		
SOCKET BODY: COPPER ALLOY	-		
SPRING: STAINLESS STEEL	APPLICATION SPEC	SIZE C	CAGE CODE 00779
FINISH	-	DRAWING NO C-202508	
SOCKET BODY: 1	WEIGHT -	SCALE 10:1	SHEET 1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.