






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		E3	REVISED PER ECR-15-007136	15MAY2015	GRZ	JL



SECTION A-A
SCALE 20:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
REF 0.76±0.05
[.030±.002] BRASS

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± 0.38 [.015]
4 PLC ± —
ANGLES ± 1° 0'

FINISH
TIN PLATE

DWN RAGHAVENDRA 13NOV06
CHK G.D.PORTA
APVD G.D.PORTA
PRODUCT SPEC
APPLICATION SPEC
WEIGHT —

TE Connectivity
NAME
SPLICE, AMPLIVAR
SIZE A3
CAGE CODE 00779
DRAWING NO C-62311
RESTRICTED TO —

CUSTOMER DRAWING
SCALE 6:1
SHEET 1 OF 1
REV E3

- 1 CONTINUOUS STRIP ON REELS.
- 2 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 3 WIRE RANGE: 10000-17000 CMA.
- 4 CRIMP WIDTH: .250 F TYPE WITH CURVED ANVIL
CRIMP HEIGHT (±.003) = (TOTAL CMA + 34,100) / 428,500

CRIMP WIDTH: .250 F TYPE WITH FLAT ANVIL
CRIMP HEIGHT (±.003) = (TOTAL CMA + 30,575) / 431,650

CRIMP WIDTH: .270 F TYPE WITH CURVED OR FLAT ANVIL
CRIMP HEIGHT (±.003) = (TOTAL CMA + 35,000) / 480,000

GENERAL APPLICATION GUIDELINES MUST BE
FOLLOWED AS SPECIFIED IN CATALOG #82221
FOR APPLICATOR INFORMATION CALL:1-800-722-1111
FOR PRODUCT INFORMATION CALL:1-800-522-6752