

## SAC-4P-M12MS/ 5,0-800

Order No.: 1457034



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1457034>

Sensor/Actuator cable, 4-position, PUR halogen-free, welding sputter-resistant, highly flexible, Gray RAL 7001, Plug, straight M12, A-coded, on Free conductor end, Cable length: 5 m

### Commercial data

|                |                                                                                                        |
|----------------|--------------------------------------------------------------------------------------------------------|
| GTIN (EAN)     | <br>4 046356 593397 |
| Note           | Made-to-order                                                                                          |
| sales group    | D111                                                                                                   |
| Pack           | 1 pcs.                                                                                                 |
| Customs tariff | 85444290                                                                                               |

### Product notes

WEEE/RoHS-compliant since:  
07/06/2010



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### General data

|                       |        |
|-----------------------|--------|
| Rated current at 40°C | 4 A    |
| Rated voltage         | 250 V  |
| Number of positions   | 4      |
| Volume resistance     | ≤ 5 mΩ |

|                                 |                                                      |
|---------------------------------|------------------------------------------------------|
| Insulation resistance           | $\geq 100 \text{ M}\Omega$                           |
| Length of cable                 | 5 m                                                  |
| Ambient temperature (operation) | -25 °C ... 90 °C (Male connector / female connector) |

#### General characteristics

|                             |                                             |
|-----------------------------|---------------------------------------------|
| Standards/regulations       | M12 connector IEC 61076-2-101               |
| Coding                      | A - standard                                |
| Surge voltage category      | II                                          |
| Pollution degree            | 3                                           |
| Degree of protection        | IP65/IP68/IP69K                             |
| Insertion/withdrawal cycles | $\geq 100$                                  |
| Contact material            | CuSn                                        |
| Contact surface material    | Ni/Au                                       |
| Contact carrier material    | TPU GF                                      |
| Material of grip body       | TPU, hardly inflammable, self-extinguishing |
| Material, knurls            | Zinc die-cast, (nickel-plated)              |
| Status display              | No                                          |


#### Conductor data

|                                    |                                                                     |
|------------------------------------|---------------------------------------------------------------------|
| Cable type                         | PUR halogen-free, highly flexible, resistant to welding beads, gray |
| Cable type (abbreviation)          | 800                                                                 |
| Cable abbreviation                 | Li12YYTPE-HF                                                        |
| Conductor cross section            | 0.34 mm <sup>2</sup>                                                |
| AWG signal line                    | 22                                                                  |
| Conductor structure signal line    | 42x 0.10 mm                                                         |
| Core diameter including insulation | 1.3 mm $\pm 0.05$ mm                                                |
| External cable diameter            | 4.8 mm $\pm 0.2$ mm                                                 |
| Wire colors                        | Black, brown, blue, white                                           |
| External sheath, color             | Gray RAL 7001                                                       |
| Insulation resistance              | $\geq 20 \text{ M}\Omega \cdot \text{km}$                           |
| Conductor resistance               | Approx. 53 $\Omega/\text{km}$                                       |
| Nominal voltage, conductor         | 300 V                                                               |
| Test voltage, conductor            | 2000 V                                                              |
| Overall twist                      | 4 wires, twisted                                                    |
| Outer sheath, material             | PUR                                                                 |
| Material conductor insulation      | PES                                                                 |

|                                               |                                                                                                                                    |
|-----------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Conductor material                            | Bare Cu litz wires                                                                                                                 |
| Smallest bending radius, fixed installation   | 24 mm                                                                                                                              |
| Smallest bending radius, movable installation | 50 mm                                                                                                                              |
| Number of bending cycles                      | 15000000                                                                                                                           |
| Bending radius                                | 50 mm                                                                                                                              |
| Traversing path                               | 0.9 m                                                                                                                              |
| Traversing rate                               | 5 m/s                                                                                                                              |
| Acceleration                                  | 30 m/s <sup>2</sup>                                                                                                                |
| Torsion force                                 | ± 360 °/m                                                                                                                          |
| Ambient temperature (operation)               | -40 °C ... 90 °C (cable, fixed installation)                                                                                       |
|                                               | -30 °C ... 90 °C (cable, flexible installation)                                                                                    |
| Special properties                            | Sheath resistant to welding beads, can be recycled, matt, without adhesion, wear-resistant, flame resistant and self-extinguishing |
|                                               | Free from silicone and cadmium                                                                                                     |
|                                               | Free of substances which would hinder coating with paint or varnish                                                                |
| Flame resistance                              | DIN VDE 0472 part 804, test type B                                                                                                 |
|                                               | IEC 60332-1                                                                                                                        |
|                                               | in accordance with FT1 as per UL 758                                                                                               |
| Halogen-free                                  | The cable is halogen-free                                                                                                          |
| Resistance to oil                             | Excellent oil-resistance (as per DIN VDE 0250 T.407)                                                                               |
| Other resistance                              | Highly resistant to acids, alkaline solutions and solvents                                                                         |


## Diagrams/Drawings

### Dimensioned drawing




M12 x 1 male connector, straight

#### Circuit diagram



Contact assignment of the M12 plug

#### Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

**Address**

PHOENIX CONTACT Inc., USA  
586 Fulling Mill Road  
Middletown, PA 17057, USA  
Phone (800) 888-7388  
Fax (717) 944-1625  
<http://www.phoenixcon.com>



© 2011 Phoenix Contact  
Technical modifications reserved;