


Central
Semiconductor Corp.

Central
Semiconductor Corp.

Central
Semiconductor Corp.

CentralTM
Semiconductor Corp.

145 Adams Avenue
Hauppauge, New York 11788



2N4901	2N4902	2N4903	PNP
2N5067	2N5068	2N5069	NPN

COMPLEMENTARY SILICON POWER
TRANSISTORS

JEDEC TO-3 CASE

DESCRIPTION

The CENTRAL SEMICONDUCTOR 2N4901, 2N5067 series types are complementary silicon power transistors manufactured by the epitaxial base process, mounted in a hermetically sealed metal case designed for general purpose switching and amplifier applications.

MAXIMUM RATINGS ($T_C=25^{\circ}\text{C}$ unless otherwise noted)

	SYMBOL ¹	2N4901 2N5067	2N4902 2N5068	2N4903 2N5069	UNIT
Collector-Base Voltage	V_{CB0}	40	60	80	V
Collector-Emitter Voltage	V_{CE0}	40	60	80	V
Emitter-Base Voltage	V_{EB0}	5.0	5.0	5.0	V
Collector Current	I_C	5.0	5.0	5.0	A
Base Current	I_B	1.0	1.0	1.0	A
Power Dissipation	P_D	87.5	87.5	87.5	W
Operating and Storage Junction Temperature T_J, T_{STG}		-65 TO +200			$^{\circ}\text{C}$
Thermal Resistance	θ_{JC}	2.0			$^{\circ}\text{C/W}$

ELECTRICAL CHARACTERISTICS ($T_C=25^{\circ}\text{C}$ unless otherwise noted)

SYMBOL	TEST CONDITIONS	2N4901 2N5067		2N4902 2N5068		2N4903 2N5069		UNIT
		MIN	MAX	MIN	MAX	MIN	MAX	
I_{CB0}	$V_{CB}=\text{Rated } V_{CB0}$ (NPN types)		1.0		1.0		1.0	mA
I_{CB0}	$V_{CB}=\text{Rated } V_{CB0}$ (PNP types)		0.1		0.1		0.1	mA
I_{CEV}	$V_{CE}=\text{Rated } V_{CE0}, V_{EB}(\text{OFF})=1.5\text{V}$ (NPN types)		1.0		1.0		1.0	mA
I_{CEV}	$V_{CE}=\text{Rated } V_{CE0}, V_{EB}(\text{OFF})=1.5\text{V}$ (PNP types)		0.1		0.1		0.1	mA
I_{CEV}	$V_{CE}=\text{Rated } V_{CE0}, V_{EB}(\text{OFF})=1.5\text{V}, T_C=150^{\circ}\text{C}$		2.0		2.0		2.0	mA
I_{CE0}	$V_{CE}=\text{Rated } V_{CE0}$		1.0		1.0		1.0	mA
I_{EB0}	$V_{BE}=5.0\text{V}$		1.0		1.0		1.0	mA
BV_{CE0}	$I_C=200\text{mA}$	40		60		80		V
$V_{CE}(\text{SAT})$	$I_C=1.0\text{A}, I_B=0.1\text{A}$		0.4		0.4		0.4	V
$V_{CE}(\text{SAT})$	$I_C=5.0\text{A}, I_B=1.0\text{A}$		1.5		1.5		1.5	V
$V_{BE}(\text{ON})$	$V_{CE}=2.0\text{V}, I_C=1.0\text{A}$		1.2		1.2		1.2	V
h_{FE}	$V_{CE}=2.0\text{V}, I_C=1.0\text{A}$	20	100	20	100	20	100	
h_{FE}	$V_{CE}=2.0\text{V}, I_C=5.0\text{A}$	7.0		7.0		7.0		
h_{fe}	$V_{CE}=10\text{V}, I_C=0.5\text{A}, f=1.0\text{kHz}$	20		20		20		
f_T	$V_{CE}=10\text{V}, I_C=1.0\text{A}, f=1.0\text{MHz}$	4.0		4.0		4.0		MHz

CentralTM
Semiconductor Corp.

145 Adams Avenue
Hauppauge, NY 11788 USA
Tel: (631) 435-1110 • Fax: (631) 435-1824
www.centralsemi.com