

PRODUCT NUMBER

73304-XXXLF

PLATING OPTION

1= GXT 0.76 μm
3= GOLD 0.76 μm
5= GOLD 1.27 μm

PACKAGE OPTION

1= TAPE ON REEL
2= TUBE
3= TAPE ON REEL
IN PLASTIC BAG


TERMINAL LOADING

1= FULLY LOADED
2= POS 1,2,7,8
3= POS 3,4,5,6

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 4.

NOTES:

- 1- MATERIAL: HOUSING: HIGH TEMP. NYLON, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μm MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXCEPT SOLDER TAIL TIPS
3 - SOLDER TAILS COPLANARITY : 0.1 mm
4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
a - PLATING:
- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μm MINIMUM MATTE TIN OVER 1.27 μm
MINIMUM NICKEL UNDERPLATE.
b - MANUFACTURING PROCESS COMPATIBILITY
- THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
c - LABELING:
- MEETS PACKAGING SPECS AS PER GS-14-920
d - LEGAL STATEMENT: SEE GS-22-008
5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
TO PROTECT FROM MOISTURE DURING STACKING TIME.









CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface	tolerance	projection	product family	
				ISO 1302	ISO 406 ISO 1101		MOD JACK	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
H	F06-0240	DLE	06.07.18	angles	±0.13		SMT RA JACK	
J	F09-0070	LSA	02.07.23	linear		mm	8 POS OUTSIDE	
K	B-15798	JFA	13.09.09	±2'		scale 2:1		
				dr	D LEGRAND	03.01.27	dwg no	
E	F03020	DLE	03.01.27	engr	F TISSERAND	03.01.27	sheet 1 of 3	
F	F04-0363	DLE	04.10.18	chr	JF NOTTEAU	03.01.27	size	
G	F05-0247	DLE	05.09.12	appo	F.TI	03.01.27	A3	
sheet				revision	K	E	type	
index				sheet	1	2	CUSTOMER Drawing	

PRODUCT NUMBER
SEE SHEET 1

LTR	PART NAME	QTY
1	PRODUCT	230
2	TAPE	1
3	REEL	1
4	COVER TAPE	1



1- IN ACCORDANCE WITH EIA-481 AND IEC 296-3

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MOD-JACK					
ltr		ecn no		dr		date		tolerances unless otherwise specified				title			
D		D80620		DLE		98.11.26		angles		linear		mm 		SMT RA JACK	
E		F06-0240		DLE		06.07.18						scale 2:1		8 POS. OUTSIDE	
								dr		D LEGRAND		04.10.18		dwg no	
								enrg		P NIZZI		04.10.18		sheet 2 of 3	
								chr		D LEGRAND		04.10.18		size	
								appd		P NIZZI		04.10.18		A3	
sheet index		revision sheet												type	
														CUSTOMER Drawing	

FCI
FCIconnect.com

Copyright FCI

