

NOTES:

1.0 ELECTRICAL SPECIFICATIONS:

1.1 FREQUENCY RANGE: DC TO 4.0 GHz

1.2 INPUT POWER:

2 WATTS @ +25°C

0.5 WATTS @ +125°C


1.3 OPERATING TEMP RANGE: -55°C TO +125°C

1.4 IMPEDANCE: 50 OHMS

1.5 VSWR: 1.20:1 MAX

2.0 MARKING: (MARK UNIT AS SHOWN)

REF: INK-02638-27-04



MODEL NUMBER

TRM-2048-MO-BNC-10

REV.	DESCRIPTION	DATE
-	RELEASED	3/21/79
A	ECR 6545 (RENUMBER)	6/29/89
B	ECN 10572	5/24/91
B1	REDRAW ON CAD	9/24/91
B2	ADDED TITLEBLOCK	10/26/05
C	ECO 23981	11/29/11

NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Emerson Network Power.		CAGE CODE 34078		MIDWEST MICROWAVE	
		 EMERSON Network Power Connectivity Solutions		TITLE TERMINATION OUTLINE DRAWING	
UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 3 PLACE DECIMALS ±.005 2 PLACE DECIMALS ±.02 FRACTIONS ±1/64 PARALLELITY: T.I.R. _____ FLATNESS: T.I.R. _____ CONCENTRICITY: T.I.R. _____ ANGLES AND PERPENDICULARITY: ±1°		DRAWN/DATE A.BEATTY 9/24/91	ENG./DATE G.KOZAK 9/24/91	DRAWING NUMBER TRM-2048-MO-BNC-10-01	
		CHECKED/DATE	APPROVED/DATE	SCALE: 5=1	REV. C
				SHEET 1 of 1	