






	10	9	8	7	6	5	4	3	2	19193
	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S"	PACKAGING					
F	I91930206	E-357-08	8	.173/(4.39)	LOOSE PIECE					
	I91930209	E-357-10	10	.198/(5.02)						
	I91930212	E-357-14	1/4	.265/(6.73)						
	I91930219	E-357-56	5/16	.328/(8.33)						
	I91930216	E-357-38	3/8	.390/(9.90)						
E	I91930223	E-357-76	7/16	.453/(11.50)	TAPE MOUNTED					
	I91930208	E-357-08T	8	.173/(4.39)						
	I91930211	E-357-10T	10	.198/(5.02)						
	I91930215	E-357-14T	1/4	.265/(6.73)						
	I91930222	E-357-56T	5/16	.328/(8.33)						
	I91930218	E-357-38T	3/8	.390/(9.90)						
	I91930224	E-357-76T	7/16	.453/(11.50)						



PARTS ON TAPE
DOUBLE SPACED AS SHOWN



- NOTE(S):
- 1. MATERIAL: COPPER .050/(1.27) THICK
 - 2. PLATING: ELECTROPLATE TIN
 - 3. ALL DIMENSIONS IN INCHES/(MM).
 - 4. WIRE SIZE: 6 AWG 16 MM²
 - 5. PART IS ROHS COMPLIANT.

SALES DRAWING

REVISED MATL THKNS		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---		DESIGN UNITS INCH		THIRD ANGLE PROJECTION	
EC NO: ET2007-0011 DRW:HEHLE 2006/07/12 CHKD: JMACNEIL 2006/07/13 APPR: RDOERSS 2006/07/17		DESCRIPTION REV		=0 =0		DRAWN BY DATE		RING TONGUE TERMINAL VERSAKRIMP 6 AWG					
						TITLED							
				mm INCH		Edb 2000/11/01		MOLEX MOLEX INCORPORATED					
				4 PLACES ± --- ± ---		CHECKED BY DATE							
				3 PLACES ± --- ±.005		HEB 2000/11/01							
				2 PLACES ± 0.13 ±.01		APPROVED BY DATE							
1 PLACE ± 0.25 ± ---		RWD 2000/11/01		SEE CHART									
ANGULAR ±1/2°		MATERIAL NO.								DOCUMENT NO.			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									