






LOC	DIST	REVISIONS					
		P	LIR	DESCRIPTION	DATE	DWN	APVD
AD	00		G	REV PER EC 0S12-0414-03	20FEB04	NK	RW
			G1	REVISED PER ECO-09-020935	26AUG09	KK	AEG

- △ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER. COLOR: NATURAL.
- △ CONTACT MATERIAL: PHOSPHOR BRONZE.
- △ CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL.
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS
0.0006 MIN TIN-LEAD OVER UNDERPLATE.
LUBRICATION (ENTIRE CONTACT):
SURFACE CONDITIONER PER AMP SPEC 112-1002 AFTER PLATING.

- △ PART MARKING LOCATED APPROXIMATELY AS SHOWN.
- △ DIMENSION APPLIES WHEN SEATED ON PRINTED CIRCUIT BOARD.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



0.54±0.05
Ø 0.20 (M) (N) (P) (R) (M)



VIEW Z-Z
SCALE 20:1

△ OBSOLETE	94.00	47	95.88	△	240	223055-8
	46.00	23	47.88	△	120	223055-4
	—	—	—	—	—	223055-3
	22.00	11	23.88	△	60	223055-2
	10.00	5	11.88	△	30	223055-1
DIM C	DIM B	DIM A	FINISH	NUMBER OF SIGNAL POSITIONS		PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN T. SHUEY CHK C. SCHMID APVD C. SCHMID	Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PIN ASSEMBLY, Z-PACK 2mm FB SIGNAL VERTICAL 5 ROW, WITH PRESS FIT LEADS		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC		SIZE A1		
MATERIAL		FINISH		WEIGHT		
△ 1 △ 2 △ 3		△ -		CUSTOMER DRAWING		
SCALE 4:1		SHEET 1 OF 1		REV G1		