

Rail Mount Fuse Holders

NDNF1 fuse holding rail mount terminal block

SPECIFICATIONS:

Rating: 30A, 600V; UL/CSA

Number Of Poles: 1

Fuse Size: 13/32" x 1-1/2"

BCC recommends BUSS® KTK-R, FNQ-R or equivalent.

Circuit Jumper: JF1, 2 Circuits

Wire Range: AWG #8-22 CU




Mounting Options: 35mm DIN rail, C-rail

Fuse Pullers : PF1 (standard);

*LPF1 (lighted neon or incandescent bulb).

Torque Rating: 18 in-lb

Operating Temperature: 105°C



PF1
Fuse Puller



LPF1
Lighted Fuse Puller

NDND1 non-fused disconnect enables isolation of individual circuits for testing

NDFD1 fused disconnect block

NDNLF1 fused disconnect with visual indicator* for blown fuse

SPECIFICATIONS:

Ratings: NDND1: 30A, 600V; UL/CSA

NDNFD1: 15A, 600V; CSA

NDNLF1: 15A, 600V

Number Of Poles: 1

Fuse size: 1/4" x 1-1/4"

BCC recommends BUSS® AGC, MDL or equivalent.

Circuit Jumper: JF1, 2 circuits



Wire Range: AWG #8-22 CU

Mounting Options: 35mm DIN rail, C-rail

Marking Tape: MT12-1/2

Torque Rating: 18 in-lb

Operating Temperature: 105°C



*Visual indicator for blown fuse is neon or incandescent bulb, depending on voltage. Specify voltage required.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[NDNFD1-WH](#) [NDNLFD1-WH](#)