

USB A/A Extension Cable (USB-A Left-Angle M to USB-A F), 10-in.

MODEL NUMBER: **U005-10I**



Highlights

- Modifies the cable connecting to a PC to 90 degrees
- 24k gold-plated connectors and gold-plated copper contacts
- 24 gauge power wires

System Requirements

- USB port and device

Package Includes

- USB 2.0 Gold Extension cable - USB "A" Left-Angle Male to USB "A" Female - 10"

Description

Tripp Lite's USB 2.0 90 degree extension cable is used to modify the cable connecting to a PC or peripheral from straight-out to 90 degrees. This conversion is invaluable when available space does not permit a straight-out USB cable. This handy USB cable features molded strain relief, double shielding, 24k gold plated connectors and gold plated copper contacts for superior conductivity and error-free data transmission. It is constructed of the highest quality wire allowed by the USB specification and consists of 24 AWG power wires to maximize the full potential of USB.

Features

- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil feature twisted 28/24 AWG data lines
- Gold plated connectors and gold plated copper contacts provide superior conductivity
- Molded connectors with built-in strain relief ensure that the cable lasts a long time

Specifications

OVERVIEW	
Intended Application	Connecting Peripherals
Style	USB
Cable Types	USB
INPUT	
Cable Length (ft.)	0.8
Cable Length (in.)	10
UPC ASSIGNMENT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Carton UPC#	037332117861
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	USB A (MALE)
Connector B	USB A (FEMALE)
CERTIFICATIONS	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.