







NON-AREA			95.81 [3.772]	86.21 [3.394]	39.37 [1.550]	31	63	64	2-111446-6			
			89.59 [3.527]	81.13 [3.194]	36.83 [1.450]	29	59	60	2-111446-5			
			70.41 [2.772]	60.81 [2.394]	26.67 [1.050]	21	43	44	2-111446-4			
			65.33 [2.572]	55.73 [2.194]	24.13 [.950]	19	39	40	2-111446-3			
			57.71 [2.272]	48.11 [1.894]	20.32 [.800]	16	33	34	2-111446-2			
			52.63 [2.072]	43.03 [1.694]	17.78 [.700]	14	29	30	2-111446-1			
			47.55 [1.872]	37.95 [1.494]	15.24 [.600]	12	25	26	2-111446-0			
			45.01 [1.772]	35.41 [1.394]	13.97 [.550]	11	23	24	1-111446-9			
			39.93 [1.572]	30.33 [1.194]	11.43 [.450]	9	19	20	1-111446-8			
			78.03 [3.072]	68.43 [2.694]	30.48 [1.200]	24	49	50	1-111446-7			
			34.85 [1.372]	25.25 [.994]	8.89 [.350]	7	15	16	1-111446-6			
			32.31 [1.272]	22.71 [.894]	7.62 [.300]	6	13	14	1-111446-5			
AREA			27.230 [1.072]	17.63 [.694]	5.08 [.200]	4	9	10	1-111446-4			
			SUPERCEDED		95.81 [3.772]	86.21 [3.394]	39.37 [1.550]	31	63	64	1-111446-3	
			OBSOLETE		89.59 [3.527]	81.13 [3.194]	36.83 [1.450]	29	59	60	1-111446-2	
			OBSOLETE		78.03 [3.072]	68.43 [2.694]	30.48 [1.200]	24	49	50	1-111446-1	
			OBSOLETE		70.41 [2.772]	60.81 [2.394]	26.67 [1.050]	21	43	44	1-111446-0	
			OBSOLETE		65.33 [2.572]	55.73 [2.194]	24.13 [.950]	19	39	40	111446-9	
			OBSOLETE		57.71 [2.272]	48.11 [1.894]	20.32 [.800]	16	33	34	111446-8	
			SUPERCEDED		52.63 [2.072]	43.03 [1.694]	17.78 [.700]	14	29	30	111446-7	
			OBSOLETE		47.55 [1.872]	37.95 [1.494]	15.24 [.600]	12	25	26	111446-6	
			OBSOLETE		45.01 [1.772]	35.41 [1.394]	13.97 [.550]	11	23	24	111446-5	
		B]				39.93 [1.572]	30.33 [1.194]	11.43 [.450]	9	19	20	111446-4
					OBSOLETE		34.85 [1.372]	25.25 [.994]	8.89 [.350]	7	15	16
	OBSOLETE				32.31 [1.272]	22.71 [.894]	7.62 [.300]	6	13	14	111446-2	
				27.230 [1.072]	17.63 [.694]	5.08 [.200]	4	9	10	111446-1		
	CONTACT FINISH			E	D	C	B	A	NO. OF POSN	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 7-11-90 H. MOLL GSK 8-1-90 F.M.HOFFEY 8-3-90		 TE Connectivity	
DIMENSIONS: mm (INCH)		TOLERANCES UNLESS OTHERWISE SPECIFIED: mm (INCH)		NAME D. HOFFMAN	
		0. PLC ± 1. PLC ± 2. PLC ± 0.13(0.005) 3. PLC ± 4. PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-1336 APPLICATION SPEC 114-7011 WEIGHT —	
MATERIAL 		CONTACTS: SEE TABLE		SIZE CAGE CODE DRAWING NO A1 00779 C 111446	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 1 REV R	