

**SURFACE MOUNT GLASS PASSIVATED  
HIGH EFFICIENCY SILICON RECTIFIER**  
**VOLTAGE RANGE 50 to 1000 Volts CURRENT 1.0 Ampere**

**FEATURES**

- \* Glass passivated device
- \* Ideal for surface mounted applications
- \* Low leakage current
- \* Metallurgically bonded construction
- \* Mounting position: Any
- \* Weight: 0.015 gram

**MECHANICAL DATA**


- \* Epoxy : Device has UL flammability classification 94V-0

**DISCONTINUED-**

"This series is replaced by the HFM10X series that meets to the same fit and function parameters and share the same solder pad layout. The HFM10X series is preferred for error-free vacuum pick-up and PCB assembly."

**MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS**

Ratings at 25 °C ambient temperature unless otherwise specified.  
Single phase, half wave, 60 Hz, resistive or inductive load.  
For capacitive load, derate current by 20%.



Dimensions in inches and (millimeters)

**MAXIMUM RATINGS (@ TA=25 °C unless otherwise noted)**

RATINGS	SYMBOL	HSM101	HSM102	HSM103	HSM104	HSM105	HSM106	HSM107	HSM108	UNITS
Maximum Recurrent Peak Reverse Voltage	V <sub>RRM</sub>	50	100	200	300	400	600	800	1000	Volts
Maximum RMS Voltage	V <sub>RMS</sub>	35	70	140	210	280	420	490	700	Volts
Maximum DC Blocking Voltage	V <sub>DC</sub>	50	100	200	300	400	600	800	1000	Volts
Maximum Average Forward Rectified Current at T <sub>A</sub> = 50°C	I <sub>O</sub>	1.0								Amps
Peak Forward Surge Current 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)	I <sub>FSM</sub>	30								Amps
Typical Junction Capacitance (Note 2)	C <sub>J</sub>	15					12			pF
Operating Temperature Range	T <sub>J</sub>	150								°C
Storage Temperature Range	T <sub>STG</sub>	-55 to + 150								°C

**ELECTRICAL CHARACTERISTICS(@TA=25 °C unless otherwise noted)**

CHARACTERISTICS		SYMBOL	HSM101	HSM102	HSM103	HSM104	HSM105	HSM106	HSM107	HSM108	UNITS
Maximum Instantaneous Forward Voltage at 1.0A DC		V <sub>F</sub>	1.0			1.3		1.7			Volts
Maximum Full Load Reverse Current, Full cycle Average T <sub>A</sub> =55°C		I <sub>R</sub>	50								μA
Maximum Average Reverse Current	@T <sub>A</sub> = 25°C		5								μA
at Rated DC Blocking Voltage	@T <sub>A</sub> = 125°C		100								μA
Maximum Reverse Recovery Time (Note 4)		trr	50					75			nSec

NOTES : 1. Measured at 1 MHz and applied reverse voltage of 4.0 volts.  
2. "Fully ROHS compliant", "100% Sn plating (Pb-free)".  
3. Test Conditions:  $I_F = 0.5\text{A}$ ,  $I_R = -1.0\text{A}$ ,  $I_{RR} = -0.25\text{A}$ .

2007-5

# RATING AND CHARACTERISTICS CURVES ( HSM101 THRU HSM108 )




FIG.1 TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTIC




FIG.2 TYPICAL FORWARD CURRENT DERATING CURVE






FIG.3 TYPICAL REVERSE CHARACTERISTICS


## RATING AND CHARACTERISTICS CURVES ( HSM101 THRU HSM108 )



**FIG.4 TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS**




**FIG.5 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT**



**FIG.6 TYPICAL JUNCTION CAPACITANCE**

## Mounting Pad Layout



Dimensions in inches and (millimeters)

## DISCLAIMER NOTICE

Rectron Inc reserves the right to make changes without notice to any product specification herein, to make corrections, modifications, enhancements or other changes. Rectron Inc or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies. Data sheet specifications and its information contained are intended to provide a product description only. "Typical" parameters which may be included on RECTRON data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. Rectron Inc does not assume any liability arising out of the application or use of any product or circuit.

Rectron products are not designed, intended or authorized for use in medical, life-saving implant or other applications intended for life-sustaining or other related applications where a failure or malfunction of component or circuitry may directly or indirectly cause injury or threaten a life without expressed written approval of Rectron Inc. Customers using or selling Rectron components for use in such applications do so at their own risk and shall agree to fully indemnify Rectron Inc and its subsidiaries harmless against all claims, damages and expenditures.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rectron:](#)

[HSM105-W](#) [HSM103-W](#) [HSM104-W](#) [HSM106-W](#) [HSM102-W](#) [HSM101-W](#)