




	10		9		8		7		6		5		4		3		2		1																																																																																																																																				
F	PART NUMBER	CKT SIZE	VOID CKT	DIM A	DIM B	DIM C	DIM D	LEGEND: A-70246 - * * * * CKT SIZE PLATING OPT. SEE TABLE FOR DETAIL <table><tr><td>△</td><td>PART NUMBER</td><td>PLATING OPTION (TIN/LEAD)</td><td>△</td><td>PART NUMBER</td><td>PLATING OPTION (TIN)</td></tr><tr><td>70246-08**</td><td>08</td><td>-</td><td>7.62</td><td>14.73</td><td>17.78</td><td>15.24</td></tr><tr><td>70246-10**</td><td>10</td><td>-</td><td>10.16</td><td>17.27</td><td>20.32</td><td>17.78</td></tr><tr><td>70246-12**</td><td>12</td><td>-</td><td>12.70</td><td>19.81</td><td>22.86</td><td>20.32</td></tr><tr><td>70246-14**</td><td>14</td><td>-</td><td>15.24</td><td>22.35</td><td>25.40</td><td>22.86</td></tr><tr><td>70246-16**</td><td>16</td><td>-</td><td>17.78</td><td>24.89</td><td>27.94</td><td>25.40</td></tr><tr><td>70246-20**</td><td>20</td><td>-</td><td>22.86</td><td>29.97</td><td>33.02</td><td>30.48</td></tr><tr><td>70246-24**</td><td>24</td><td>-</td><td>27.94</td><td>35.05</td><td>38.10</td><td>35.56</td></tr><tr><td>70246-26**</td><td>26</td><td>-</td><td>30.48</td><td>37.59</td><td>40.64</td><td>38.10</td></tr><tr><td>70246-30**</td><td>30</td><td>-</td><td>35.56</td><td>42.67</td><td>45.72</td><td>43.18</td></tr><tr><td>70246-34**</td><td>34</td><td>-</td><td>40.64</td><td>47.75</td><td>50.80</td><td>48.26</td></tr><tr><td>70246-40**</td><td>40</td><td>-</td><td>48.26</td><td>55.37</td><td>58.42</td><td>55.88</td></tr><tr><td>70246-44**</td><td>44</td><td>-</td><td>53.34</td><td>60.45</td><td>63.50</td><td>60.96</td></tr><tr><td>70246-50**</td><td>50</td><td>-</td><td>60.96</td><td>68.07</td><td>71.12</td><td>68.58</td></tr><tr><td>70246-56**</td><td>56</td><td>-</td><td>68.58</td><td>75.69</td><td>78.74</td><td>76.20</td></tr><tr><td>70246-60**</td><td>60</td><td>-</td><td>73.66</td><td>80.77</td><td>83.82</td><td>81.28</td></tr><tr><td>70246-64**</td><td>64</td><td>-</td><td>78.74</td><td>85.85</td><td>88.90</td><td>86.36</td></tr><tr><td>70246-72**</td><td>72</td><td>-</td><td>88.90</td><td>96.01</td><td>99.06</td><td>96.52</td></tr><tr><td>70246-25**</td><td>26</td><td>26</td><td>30.48</td><td>37.59</td><td>40.64</td><td>38.10</td></tr></table>												△	PART NUMBER	PLATING OPTION (TIN/LEAD)	△	PART NUMBER	PLATING OPTION (TIN)	70246-08**	08	-	7.62	14.73	17.78	15.24	70246-10**	10	-	10.16	17.27	20.32	17.78	70246-12**	12	-	12.70	19.81	22.86	20.32	70246-14**	14	-	15.24	22.35	25.40	22.86	70246-16**	16	-	17.78	24.89	27.94	25.40	70246-20**	20	-	22.86	29.97	33.02	30.48	70246-24**	24	-	27.94	35.05	38.10	35.56	70246-26**	26	-	30.48	37.59	40.64	38.10	70246-30**	30	-	35.56	42.67	45.72	43.18	70246-34**	34	-	40.64	47.75	50.80	48.26	70246-40**	40	-	48.26	55.37	58.42	55.88	70246-44**	44	-	53.34	60.45	63.50	60.96	70246-50**	50	-	60.96	68.07	71.12	68.58	70246-56**	56	-	68.58	75.69	78.74	76.20	70246-60**	60	-	73.66	80.77	83.82	81.28	70246-64**	64	-	78.74	85.85	88.90	86.36	70246-72**	72	-	88.90	96.01	99.06	96.52	70246-25**	26	26	30.48	37.59	40.64	38.10
	△	PART NUMBER	PLATING OPTION (TIN/LEAD)	△	PART NUMBER	PLATING OPTION (TIN)																																																																																																																																																	
	70246-08**	08	-	7.62	14.73	17.78	15.24																																																																																																																																																
	70246-10**	10	-	10.16	17.27	20.32	17.78																																																																																																																																																
	70246-12**	12	-	12.70	19.81	22.86	20.32																																																																																																																																																
	70246-14**	14	-	15.24	22.35	25.40	22.86																																																																																																																																																
70246-16**	16	-	17.78	24.89	27.94	25.40																																																																																																																																																	
70246-20**	20	-	22.86	29.97	33.02	30.48																																																																																																																																																	
70246-24**	24	-	27.94	35.05	38.10	35.56																																																																																																																																																	
70246-26**	26	-	30.48	37.59	40.64	38.10																																																																																																																																																	
70246-30**	30	-	35.56	42.67	45.72	43.18																																																																																																																																																	
70246-34**	34	-	40.64	47.75	50.80	48.26																																																																																																																																																	
70246-40**	40	-	48.26	55.37	58.42	55.88																																																																																																																																																	
70246-44**	44	-	53.34	60.45	63.50	60.96																																																																																																																																																	
70246-50**	50	-	60.96	68.07	71.12	68.58																																																																																																																																																	
70246-56**	56	-	68.58	75.69	78.74	76.20																																																																																																																																																	
70246-60**	60	-	73.66	80.77	83.82	81.28																																																																																																																																																	
70246-64**	64	-	78.74	85.85	88.90	86.36																																																																																																																																																	
70246-72**	72	-	88.90	96.01	99.06	96.52																																																																																																																																																	
70246-25**	26	26	30.48	37.59	40.64	38.10																																																																																																																																																	
E																																																																																																																																																							
D																																																																																																																																																							
C																																																																																																																																																							
B																																																																																																																																																							
A																																																																																																																																																							
ib_frame_A3_P_ME_T Rev. D 2004/04/02		9	8	7	6	5	4	3	2	1																																																																																																																																													