


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
			S1	REVISED PER ECO-11-005294	11APR11
					HMR

⚠ CHECK CABLE RANGE FOR SATISFACTORY PERFORMANCE ON SPECIFIC CABLE TO BE USED.

TABULATION				
PART NO.	COLOR	DIM."A" REF	DIM."B" REF	APPROX CABLE DIA ⚠
229910-1	BLACK	.375	.100	.350-.425
1-229910-1	BLACK	.470	.195	.425-.500
229910-4	GRAY	.375	.100	.350-.425
1-229910-4	GRAY	.470	.195	.425-.500
2-229910-1	BLACK	.375	.050	.325-.370
2-229910-4	GRAY	.375	.050	.325-.370
3-229910-1	BLACK	.375	.015	.300
3-229910-4	GRAY	.375	.015	.300
4-229910-1	BLACK	.535	.260	.550



				PART NO	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .015 ANGLES ± 1°		CONTRACT NO		TE Connectivity	
		DR <i>Joel H. Wooten</i> 4-18-86 CHK <i>Stephen Doss</i> 5/7/86			
MATERIAL		APPRO		NAME	
THERMOPLASTIC		APPRO <i>D. Trammel</i> 5/14/86		CLAMP, CABLE	
FINISH		DSGN APPD		SIZE	FSCM NO
		OTHER APPD		B	00779
				DRAWING NO	
				229910	
				SCALE 2:1	SHEET 1 OF 1