

9329 Multi-Conductor - 300V Power-Limited Tray Cable

**Description:**

22 AWG pairs stranded (7x30) tinned copper conductors, twisted pairs, PVC insulation, individually shielded, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
3	22	7x30	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material	Dia. (in.)
PVC - Polyvinyl Chloride	.062

Inner Shield**Inner Shield Material:**

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: 7x30

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.042

Outer Jacket Ripcord: Yes

Overall Cabling**Overall Cabling Lay Length & Direction:**

Direction
Left-hand Lay

Overall Nominal Diameter: 0.341 in.

Pair**Pair Color Code Chart:**

Number	Color
1	Black & Red and Numbered 1
2	Black & Red and Numbered 2
3	Black & Red and Numbered 3
Communication Wire	Orange

9329 Multi-Conductor - 300V Power-Limited Tray Cable

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +105°C
Bulk Cable Weight:	60 lbs/1000 ft.
Max. Recommended Pulling Tension:	54 lbs.
Min. Bend Radius (Install)/Minor Axis:	3.500 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	PLTC, ITC, CMG
CEC/C(UL) Specification:	CMG
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4 Loading
C(UL) Flame Test:	FT4
IEEE Flame Test:	1202
ICEA Flame Test:	T-29-520

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes
Sunlight Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)

Surface Printing:	LEGEND: BELDEN 9329 E34972 3PR22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG----FT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET
-------------------	--

Electrical Characteristics (Overall)**Nom. Inductance:**

Inductance (μH/ft)

.21

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

45

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

26

Nom. Conductor DC Resistance:

9329 Multi-Conductor - 300V Power-Limited Tray Cable

DCR @ 20°C (Ohm/1000 ft)

15

Ind. Pair Nominal Shield DC Resistance @ 20
Deg. C: 76 Ohm/1000 ft

Max. Operating Voltage - UL:**Voltage**

300 V RMS (PLTC

CMG)

150 V RMS (ITC)

Max. Recommended Current:**Current**

3.4 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9329 0601000	1,000 FT	60.000 LB	CHROME	C	3 #22 FS PR PVC PVC
9329 060500	500 FT	29.500 LB	CHROME	C	3 #22 FS PR PVC PVC

Notes:


C = CRATE REEL PUT-UP.

UL Instrumentation Cable**300V Power-Limited Tray Cables****Industrial Grade Sunlight- and Oil-Resistant Jackets**

Description	Part No.	No. of Pairs/Triads	Color Code	Standard Lengths		Standard Unit Weight		Jacket Thickness		Nominal OD		Maximum Pull Tension		Minimum Bend Radius	
				ft.	m	Lbs.	kg	Inch	mm	Inch	mm	Lbs.	N	Inch	mm

22 AWG Pairs Stranded (7x30) Tinned Copper Conductors • Twisted Pairs**Individually Shielded • PVC Insulation • Chrome PVC Jacket**


NEC: PLTC, ITC, CMG
CEC: CMG FT4
IEEE 1202/383
ICEA T-29-520



9328	2	E2	500 1000	152.4 304.8	23.5 46.0	10.2 20.9	.042	1.07	.323	8.20	54	240	3.00	76.20
9329	3	E2	500 1000	152.4 304.8	29.5 60.0	13.4 27.3	.042	1.07	.341	8.66	54	240	3.50	88.90
9330	4	E2	500 1000	152.4 304.8	39.0 75.0	17.7 34.0	.042	1.07	.372	9.45	110	489	3.50	88.90
9331	6	E2	500 1000	152.4 304.8	55.0 111.0	24.5 50.4	.053	1.35	.457	11.61	101	449	4.33	109.98
9332	9	E2	500 1000	152.4 304.8	75.0 145.0	34.1 65.9	.053	1.35	.530	13.46	160	711	5.00	127.00
9333	11	E2	500 1000	152.4 304.8	89.0 177.0	40.5 80.5	.053	1.35	.592	15.04	160	711	5.50	139.70
9335	19	E2	500 1000	152.4 304.8	141.5 287.0	64.3 130.5	.063	1.60	.711	18.06	264	1174	6.50	165.10

22 AWG Pairs Stranded (7x30) Bare Copper Conductors* • Twisted Pairs**Individually Shielded + Overall Beldfoil® Shield (100% Coverage) • PVC Insulation • PVC Jacket (Black or Chrome)**

NEC: PLTC, ITC, CMG
CEC: CMG FT4
IEEE 1202/383
ICEA T-29-520



3001A[†]	2	E1	Bulk ^{††}	Bulk	—	—	.042	1.07	.324	8.23	54	240	3.25	82.55
3005A[†]	4	E1	Bulk ^{††}	Bulk	—	—	.043	1.09	.360	9.14	115	511	3.50	88.90
3007A[†]	8	E1	Bulk ^{††}	Bulk	—	—	.053	1.35	.497	12.62	250	1112	5.25	133.35
3009A[†]	12	E1	Bulk ^{††}	Bulk	—	—	.053	1.35	.570	14.48	300	1334	5.75	146.05
3011A[†]	16	E1	Bulk ^{††}	Bulk	—	—	.064	1.63	.674	17.12	350	1557	6.25	158.75
3013A[†]	24	E1	Bulk ^{††}	Bulk	—	—	.065	1.65	.800	20.32	540	2402	8.00	203.20
3015A[†]	50	E1	Bulk ^{††}	Bulk	—	—	.075	1.91	1.050	26.67	1330	5916	10.50	266.70

22 AWG Triads Stranded (7x30) Tinned Copper Conductors • Twisted Triads**Unshielded • PVC Insulation • Chrome PVC Jacket**


NEC: PLTC, ITC, CMG
CEC: CMG FT4
IEEE 1202/383
ICEA T-29-520



9491	1	E1	U-500 U-1000	U-152.4 U-304.8	12.5 23.0	5.7 10.4	.037	.94	.208	5.28	29	129	2.00	50.80
-------------	---	----	-----------------	--------------------	--------------	-------------	------	-----	------	------	----	-----	------	-------

Overall Beldfoil Shield (100% Coverage) • PVC Insulation • Chrome PVC Jacket


NEC: PLTC, ITC, CMG
CEC: CMG FT4
IEEE 1202/383
ICEA T-29-520



9363	1	E1	U-500 U-1000	U-152.4 U-304.8	13.5 26.0	6.1 11.8	.037	.94	.208	5.28	29	129	2.00	50.80
-------------	---	----	-----------------	--------------------	--------------	-------------	------	-----	------	------	----	-----	------	-------

22 AWG Triads Stranded (7x30) Bare Copper Conductors* • Twisted Triads**Overall Beldfoil Shield (100% Coverage) • PVC Insulation • PVC Jacket (Black or Chrome)**

NEC: PLTC, ITC, CMG
CEC: CMG FT4
IEEE 1202/383
ICEA T-29-520




3002A	2	E1	Bulk ^{††}	Bulk	—	—	.043	1.09	.330	8.38	62	275	3.50	88.90
--------------	---	----	--------------------	------	---	---	------	------	------	------	----	-----	------	-------

For Exposed Run rated cable, order 3002AE

Individually Shielded + Overall Beldfoil Shield (100% Coverage) • PVC Insulation • PVC Jacket (Black or Chrome)

NEC: PLTC, ITC, CMG
CEC: CMG FT4
IEEE 1202/383
ICEA T-29-520



3003A	2	E1	Bulk ^{††}	Bulk	—	—	.043	1.09	.330	8.38	82	364	3.25	82.55
--------------	---	----	--------------------	------	---	---	------	------	------	------	----	-----	------	-------

For Exposed Run rated cable, order 3003AE

*For tinned copper conductors, order with B suffix.

[†]For Exposed Run rated 3000 series cables, order with "E" suffix, e.g. 3001AE.

E1, E2 = Refer to Technical Information section for color code. Alternate color coding available upon request.

Multiple pair or triad cables have each pair/triad numbered for ease of identification.

^{††}Bulk = Check length available for specific construction.

BELDEN