

Features

- Narrow Bandwidth
- Excellent Rejection
- Excellent Return Loss


Description

Surface mount, silver (Ag) coated ceramic filter. Developed for use in CATV applications.

Weight: 16.0 grams typical

Material: Filter is composed of a ceramic block plated with Ag.

Filter complies with RoHS standards.




**Electrical Specifications**

Parameter	Frequency (MHz)	Typical @ 25°C	Spec. @ 25°C
Passband Insertion Loss	1052-1056	4.03 dB	4.03 dB max
Passband Return Loss	1052-1056	15.6 dB	15.6 dB min
Attenuation	1029	60.2 dB	60.2 dB min
Attenuation	1044	24.2 dB	24.2 dB min
Attenuation	1064	24.3	24.3 dB min
Attenuation	1079	70.2	70.2 dB min
Power into any port			1 Watt max

Note: Supplier shall test each filter to the critical electrical specifications of the above table. Any subsequent audits may deviate from in value due to measurement repeatability among different test systems. Such deviations shall not exceed the following limits:


Specification Allowance	
Insertion Loss	0.1 dB
Return Loss	1.0 dB
Stopbands	1.0 dB

Mechanical Drawing




Dim	Nominal (mm)	Tolerance (mm) +/- or max
A	47.921	max
B	10.541	max
C	7.850	max
D	18.212	0.127
E	18.212	0.127
F	1.651	0.127
G	0.635	0.127
I	1.397	0.127
J	0.635	0.127

Electrical response




PCB Layout



Packaging and Marking

KFF 6433A
CTS YWW



7 15 Slot Gray Foam Trays
(210 max per box)