

MY-type Twin Wheel Caster




Characteristic

Small turning radius with its twin wheels.

Application

Office automation appliances /
Office utilities, etc.


MY4N□S / MY6N□S (with stopper)



Specification

Model No.	Material		Allowable Load (kg)	Net Weight (g)	Code No.
	Body	Wheel			
MY4	ZDC	PA	50	128	9896
MY4S				136	9905
MY4N3				110	9899
MY4N3S				118	9908
MY4N10				113	9901
MY4N10S				122	9910
MY6			80	215	9897
MY6S				227	9906
MY6N3				187	9902
MY6N3S				198	9911
MY6N12				188	9904
MY6N12S				199	9913

MY4S / MY6S (with stopper)



Size List

Model No.	A	B	C	D	E	G	d	H1	H2	J1	J2	K	L	W1	W2
MY4	36.5	φ34	φ46	φ40	12.5	φ5	W3/8	60	53	t2.3	t4.5	14	12	39	15
MY4S															
MY4N3															
MY4N3S															
MY4N10															
MY4N10S	36.5						M10						19		
MY6	47	φ40	φ54	φ50	17	φ5.5	W3/8	74.5	67	t3	t6	17	19	45	18
MY6S															
MY6N3															
MY6N3S															
MY6N12															
MY6N12S	47						M12						14		

※N shows the screw type on the model No. Caster with stopper has S at the end of the model No.