


HORIZONTAL & MODIFIED HEADERS

(2.00 mm) .0787" PITCH • MMT/MTMM SERIES



MMT/MTMM

Board Mates:

CLT, SQT*, SQW, ESQT,
TLE, SMM, MMS

Cable Mates:

TCSD

*Important Note:

SQT will not mate to the
MMT -02 lead style.

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over
50 μ" (1.27 μm) Ni

Operating Temp Range:

-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity (MMT):

(0.10 mm) .004" max (02-25)

(0.15 mm) .006" max (26-36)*

*(.004" stencil solution
may be available; contact
ipg@samtec.com)

MMT	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OPTION
		02 thru 36				
			-01 = (3.20 mm) .126" post	-F = Gold flash on post, Matte Tin on tail	-SH = Single Row	-K = (4.00 mm) .157" DIA Polyimide Film Pick & Place Pad (3 positions min.)
			-02 = (4.45 mm) .175" post	-L = 10 μ" (0.25 μm) Gold post, Matte Tin on tail	-DH = Double Row	-P = Pick & Place Pad (2 positions min.)
				-T = Matte Tin	-MT = Double Row Mixed Technology	-“XXX” = Polarized Position Specify position of omitted pin
						-TR = Tape & Reel
						-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)

Diagram 1: MMT -SH
No. of positions x (2.00) .0787
(2.00) .0787

Diagram 2: MMT -DH
No. of positions x (2.00) .0787
(4.00) .157

Diagram 3: MMT -MT
(2.00) .0787

Diagram 4: MMT -SH
POST
(2.79) .110
(6.22) .245

Diagram 5: MMT -MT
(2.54) .100
POST
(6.22) .245
(2.79) .110

Diagram 6: MMT -SH
(2.79) .110
(6.22) .245

Diagram 7: MMT -MT
(2.79) .110
(6.22) .245

Diagram 8: MMT -SH
(2.79) .110
(6.22) .245

Diagram 9: MMT -MT
(2.79) .110
(6.22) .245

Diagram 10: MMT -SH
(2.79) .110
(6.22) .245

Diagram 11: MMT -MT
(2.79) .110
(6.22) .245

Diagram 12: MMT -SH
(2.79) .110
(6.22) .245

Diagram 13: MMT -MT
(2.79) .110
(6.22) .245

Diagram 14: MMT -SH
(2.79) .110
(6.22) .245

Diagram 15: MMT -MT
(2.79) .110
(6.22) .245

Diagram 16: MMT -SH
(2.79) .110
(6.22) .245

Diagram 17: MMT -MT
(2.79) .110
(6.22) .245

Diagram 18: MMT -SH
(2.79) .110
(6.22) .245

Diagram 19: MMT -MT
(2.79) .110
(6.22) .245

Diagram 20: MMT -SH
(2.79) .110
(6.22) .245

Diagram 21: MMT -MT
(2.79) .110
(6.22) .245

Diagram 22: MMT -SH
(2.79) .110
(6.22) .245

Diagram 23: MMT -MT
(2.79) .110
(6.22) .245

Diagram 24: MMT -SH
(2.79) .110
(6.22) .245

Diagram 25: MMT -MT
(2.79) .110
(6.22) .245

Diagram 26: MMT -SH
(2.79) .110
(6.22) .245

Diagram 27: MMT -MT
(2.79) .110
(6.22) .245

Diagram 28: MMT -SH
(2.79) .110
(6.22) .245

Diagram 29: MMT -MT
(2.79) .110
(6.22) .245

Diagram 30: MMT -SH
(2.79) .110
(6.22) .245

Diagram 31: MMT -MT
(2.79) .110
(6.22) .245

Diagram 32: MMT -SH
(2.79) .110
(6.22) .245

Diagram 33: MMT -MT
(2.79) .110
(6.22) .245

Diagram 34: MMT -SH
(2.79) .110
(6.22) .245

Diagram 35: MMT -MT
(2.79) .110
(6.22) .245

Diagram 36: MMT -SH
(2.79) .110
(6.22) .245

Diagram 37: MMT -MT
(2.79) .110
(6.22) .245

Diagram 38: MMT -SH
(2.79) .110
(6.22) .245

Diagram 39: MMT -MT
(2.79) .110
(6.22) .245

Diagram 40: MMT -SH
(2.79) .110
(6.22) .245

Diagram 41: MMT -MT
(2.79) .110
(6.22) .245

Diagram 42: MMT -SH
(2.79) .110
(6.22) .245

Diagram 43: MMT -MT
(2.79) .110
(6.22) .245

Diagram 44: MMT -SH
(2.79) .110
(6.22) .245

Diagram 45: MMT -MT
(2.79) .110
(6.22) .245

Diagram 46: MMT -SH
(2.79) .110
(6.22) .245

Diagram 47: MMT -MT
(2.79) .110
(6.22) .245

Diagram 48: MMT -SH
(2.79) .110
(6.22) .245

Diagram 49: MMT -MT
(2.79) .110
(6.22) .245

Diagram 50: MMT -SH
(2.79) .110
(6.22) .245

Diagram 51: MMT -MT
(2.79) .110
(6.22) .245

Diagram 52: MMT -SH
(2.79) .110
(6.22) .245

Diagram 53: MMT -MT
(2.79) .110
(6.22) .245

Diagram 54: MMT -SH
(2.79) .110
(6.22) .245

Diagram 55: MMT -MT
(2.79) .110
(6.22) .245

Diagram 56: MMT -SH
(2.79) .110
(6.22) .245

Diagram 57: MMT -MT
(2.79) .110
(6.22) .245

Diagram 58: MMT -SH
(2.79) .110
(6.22) .245

Diagram 59: MMT -MT
(2.79) .110
(6.22) .245

Diagram 60: MMT -SH
(2.79) .110
(6.22) .245

Diagram 61: MMT -MT
(2.79) .110
(6.22) .245

Diagram 62: MMT -SH
(2.79) .110
(6.22) .245

Diagram 63: MMT -MT
(2.79) .110
(6.22) .245

Diagram 64: MMT -SH
(2.79) .110
(6.22) .245

Diagram 65: MMT -MT
(2.79) .110
(6.22) .245

Diagram 66: MMT -SH
(2.79) .110
(6.22) .245

Diagram 67: MMT -MT
(2.79) .110
(6.22) .245

Diagram 68: MMT -SH
(2.79) .110
(6.22) .245

Diagram 69: MMT -MT
(2.79) .110
(6.22) .245

Diagram 70: MMT -SH
(2.79) .110
(6.22) .245

Diagram 71: MMT -MT
(2.79) .110
(6.22) .245

Diagram 72: MMT -SH
(2.79) .110
(6.22) .245

Diagram 73: MMT -MT
(2.79) .110
(6.22) .245

Diagram 74: MMT -SH
(2.79) .110
(6.22) .245

Diagram 75: MMT -MT
(2.79) .110
(6.22) .245

Diagram 76: MMT -SH
(2.79) .110
(6.22) .245

Diagram 77: MMT -MT
(2.79) .110
(6.22) .245

Diagram 78: MMT -SH
(2.79) .110
(6.22) .245

Diagram 79: MMT -MT
(2.79) .110
(6.22) .245

Diagram 80: MMT -SH
(2.79) .110
(6.22) .245

Diagram 81: MMT -MT
(2.79) .110
(6.22) .245

Diagram 82: MMT -SH
(2.79) .110
(6.22) .245

Diagram 83: MMT -MT
(2.79) .110
(6.22) .245

Diagram 84: MMT -SH
(2.79) .110
(6.22) .245

Diagram 85: MMT -MT
(2.79) .110
(6.22) .245

Diagram 86: MMT -SH
(2.79) .110
(6.22) .245

Diagram 87: MMT -MT
(2.79) .110
(6.22) .245

Diagram 88: MMT -SH
(2.79) .110
(6.22) .245

Diagram 89: MMT -MT
(2.79) .110
(6.22) .245

Diagram 90: MMT -SH
(2.79) .110
(6.22) .245

Diagram 91: MMT -MT
(2.79) .110
(6.22) .245

Diagram 92: MMT -SH
(2.79) .110
(6.22) .245

Diagram 93: MMT -MT
(2.79) .110
(6.22) .245

Diagram 94: MMT -SH
(2.79) .110
(6.22) .245

Diagram 95: MMT -MT
(2.79) .110
(6.22) .245

Diagram 96: MMT -SH
(2.79) .110
(6.22) .245

Diagram 97: MMT -MT
(2.79) .110
(6.22) .245

Diagram 98: MMT -SH
(2.79) .110
(6.22) .245

Diagram 99: MMT -MT
(2.79) .110
(6.22) .245

Diagram 100: MMT -SH
(2.79) .110
(6.22) .245

Diagram 101: MMT -MT
(2.79) .110
(6.22) .245

Diagram 102: MMT -SH
(2.79) .110
(6.22) .245

Diagram 103: MMT -MT
(2.79) .110
(6.22) .245

Diagram 104: MMT -SH
(2.79) .110
(6.22) .245

Diagram 105: MMT -MT
(2.79) .110
(6.22) .245

Diagram 106: MMT -SH
(2.79) .110
(6.22) .245

Diagram 107: MMT -MT
(2.79) .110
(6.22) .245

Diagram 108: MMT -SH
(2.79) .110
(6.22) .245

Diagram 109: MMT -MT
(2.79) .110
(6.22) .245

Diagram 110: MMT -SH
(2.79) .110
(6.22) .245

Diagram 111: MMT -MT
(2.79) .110
(6.22) .245

Diagram 112: MMT -SH
(2.79) .110
(6.22) .245

Diagram 113: MMT -MT
(2.79) .110
(6.22) .245

Diagram 114: MMT -SH
(2.79) .110
(6.22) .245

Diagram 115: MMT -MT
(2.79) .110
(6.22) .245

Diagram 116: MMT -SH
(2.79) .110
(6.22) .245

Diagram 117: MMT -MT
(2.79) .110
(6.22) .245

Diagram 118: MMT -SH
(2.79) .110
(6.22) .245

Diagram 119: MMT -MT
(2.79) .110
(6.22) .245

Diagram 120: MMT -SH
(2.79) .110
(6.22) .245

Diagram 121: MMT -MT
(2.79) .110
(6.22) .245

Diagram 122: MMT -SH
(2.79) .110
(6.22) .245

Diagram 123: MMT -MT
(2.79) .110
(6.22) .245

Diagram 124: MMT -SH
(2.79) .110
(6.22) .245

Diagram 125: MMT -MT
(2.79) .110
(6.22) .245

Diagram 126: MMT -SH
(2.79) .110
(6.22) .245

Diagram 127: MMT -MT
(2.79) .110
(6.22) .245

Diagram 128: MMT -SH
(2.79) .110
(6.22) .245

Diagram 129: MMT -MT
(2.79) .110
(6.22) .245

Diagram 130: MMT -SH
(2.79) .110
(6.22) .245

Diagram 131: MMT -MT
(2.79) .110
(6.22) .245

Diagram 132: MMT -SH
(2.79) .110
(6.22) .245

Diagram 133: MMT -MT
(2.79) .110
(6.22) .245

Diagram 134: MMT -SH
(2.79) .110
(6.22) .245

Diagram 135: MMT -MT
(2.79) .110
(6.22) .245

Diagram 136: MMT -SH
(2.79) .110
(6.22) .245

Diagram 137: MMT -MT
(2.79) .110
(6.22) .245

Diagram 138: MMT -SH
(2.79) .110
(6.22) .245

Diagram 139: MMT -MT
(2.79) .110
(6.22) .245

Diagram 140: MMT -SH
(2.79) .110
(6.22) .245

Diagram 141: MMT -MT
(2.79) .110
(6.22) .245

Diagram 142: MMT -SH
(2.79) .110
(6.22) .245

Diagram 143: MMT -MT
(2.79) .110
(6.22) .245

Diagram 144: MMT -SH
(2.79) .110
(6.22) .245

Diagram 145: MMT -MT
(2.79) .110
(6.22) .245

Diagram 146: MMT -SH
(2.79) .110
(6.22) .245

Diagram 147: MMT -MT
(2.79) .110
(6.22) .245

Diagram 148: MMT -SH
(2.79) .110
(6.22) .245

Diagram 149: MMT -MT
(2.79) .110
(6.22) .245

Diagram 150: MMT -SH
(2.79) .110
(6.22) .245

Diagram 151: MMT -MT
(2.79) .110
(6.22) .245

Diagram 152: MMT -SH
(2.79) .110
(6.22) .245

Diagram 153: MMT -MT
(2.79) .110
(6.22) .245

Diagram 154: MMT -SH
(2.79) .110
(6.22) .245

Diagram 155: MMT -MT
(2.79) .110
(6.22) .245

Diagram 156: MMT -SH
(2.79) .110
(6.22) .245

Diagram 157: MMT -MT
(2.79) .110
(6.22) .245

Diagram 158: MMT -SH
(2.79) .110
(6.22) .245

Diagram 159: MMT -MT
(2.79) .110
(6.22) .245

Diagram 160: MMT -SH
(2.79) .110
(6.22) .245

Diagram 161: MMT -MT
(2.79) .110
(6.22) .245

Diagram 162: MMT -SH
(2.79) .110
(6.22) .245

Diagram 163: MMT -MT
(2.79) .110
(6.22) .245

Diagram 164: MMT -SH
(2.79) .110
(6.22) .245

Diagram 165: MMT -MT
(2.79) .110
(6.22) .245

Diagram 166: MMT -SH
(2.79) .110
(6.22) .245

Diagram 167: MMT -MT
(2.79) .110
(6.22) .245

Diagram 168: MMT -SH
(2.79) .110
(6.22) .245

Diagram 169: MMT -MT
(2.79) .110
(6.22) .245

Diagram 170: MMT -SH
(2.79) .110
(6.22) .245

Diagram 171: MMT -MT
(2.79) .110
(6.22) .245

Diagram 172: MMT -SH
(2.79) .110
(6.22) .245

Diagram 173: MMT -MT
(2.79) .110
(6.22) .245

Diagram 174: MMT -SH
(2.79) .110
(6.22) .245

Diagram 175: MMT -MT
(2.79) .110
(6.22) .245

Diagram 176: MMT -SH
(2.79) .110
(6.22) .245

Diagram 177: MMT -MT
(2.79) .110
(6.22) .245

Diagram 178: MMT -SH
(2.79) .110
(6.22) .245

Diagram 179: MMT -MT
(2.79) .110
(6.22) .245

Diagram 180: MMT -SH
(2.79) .110
(6.22) .245

Diagram 181: MMT -MT
(2.79) .110
(6.22) .245

Diagram 182: MMT -SH
(2.79) .110
(6.22) .245

Diagram 183: MMT -MT
(2.79) .110
(6.22) .245

Diagram 184: MMT -SH
(2.79) .110
(6.22) .245

Diagram 185: MMT -MT
(2.79) .110
(6.22) .245

Diagram 186: MMT -SH
(2.79) .110
(6.22) .245

Diagram 187: MMT -MT
(2.79) .110
(6.22) .245

Diagram 188: MMT -SH
(2.79) .110
(6.22) .245

Diagram 189: MMT -MT
(2.79) .110
(6.22) .245

Diagram 190: MMT -SH
(2.79) .110
(6.22) .245

Diagram 191: MMT -MT
(2.79) .110
(6.22) .245

Diagram 192: MMT -SH
(2.79) .110
(6.22) .245

Diagram 193: MMT -MT
(2.79) .110
(6.22) .245

Diagram 194: MMT -SH
(2.79) .110
(6.22) .245

Diagram 195: MMT -MT
(2.79) .110
(6.22) .245

Diagram 196: MMT -SH
(2.79) .110
(6.22) .245

Diagram 197: MMT -MT
(2.79) .110
(6.22) .245

Diagram 198: MMT -SH
(2.79) .110
(6.22) .245

Diagram 199: MMT -MT
(2.79) .110
(6.22) .245

Diagram 200: MMT -SH
(2.79) .110
(6.22) .245

Diagram 201: MMT -MT
(2.79) .110
(6.22) .245

Diagram 202: MMT -SH
(2.79) .110
(6.22) .245

Diagram 203: MMT -MT
(2.79) .110
(6.22) .245

Diagram 204: MMT -SH
(2.79) .110
(6.22) .245

Diagram 205: MMT -MT
(2.79) .110
(6.22) .245

Diagram 206: MMT -SH
(2.79) .110
(6.22) .245

Diagram 207: MMT -MT
(2.79) .110
(6.22) .245

Diagram 208: MMT -SH
(2.79) .110
(6.22) .245

Diagram 209: MMT -MT
(2.79) .110
(6.22) .245

Diagram 210: MMT -SH
(2.79) .110
(6.22) .245

Diagram 211: MMT -MT
(2.79) .110
(6.22) .245

Diagram 212: MMT -SH
(2.79) .110
(6.22) .245

Diagram 213: MMT -MT
(2.79) .110
(6.22) .245

Diagram 214: MMT -SH
(2.79) .110
(6.22) .245

Diagram 215: MMT -MT
(2.79) .110
(6.22) .245

Diagram 216: MMT -SH
(2.79) .110
(6.22) .245

Diagram 217: MMT -MT
(2.79) .110
(6.22) .245

Diagram 218: MMT -SH
(2.79) .110
(6.22) .245

Diagram 219: MMT -MT
(2.79) .110
(6.22) .245

Diagram 220: MMT -SH
(2.79) .110
(6.22) .245

Diagram 221: MMT -MT
(2.79) .110
(6.22) .245

Diagram 222: MMT -SH
(2.79) .110
(6.22) .245

Diagram 223: MMT -MT
(2.79) .110
(6.22) .245

Diagram 224: MMT -SH
(2.79) .110
(6.22) .245

Diagram 225: MMT -MT
(2.79) .110
(6.22) .245

Diagram 226: MMT -SH
(2.79) .110
(6.22) .245

Diagram 227: MMT -MT
(2.79) .110
(6.22) .245

Diagram 228: MMT -SH
(2.79) .110
(6.22) .245

Diagram 229: MMT -MT
(2.79) .110
(6.22) .245

Diagram 230: MMT -SH
(2.79) .110
(6.22) .245

Diagram 231: MMT -MT
(2.79) .110
(6.22) .245

Diagram 232: MMT -SH
(2.79) .110
(6.22) .245

Diagram 233: MMT -MT
(2.79) .110
(6.22) .245

Diagram 234: MMT -SH
(2.79) .110
(6.22) .245

Diagram 235: MMT -MT
(2.79) .110
(6.22) .245

Diagram 236: MMT -SH