






HONEYWELL
PART NUMBER
RPNS180HD1B11A

REV	CHANGE DOCUMENT	CHANGED BY	CHECK
A	0040247	VS 23JUN08	BLR

Technical Data	
Function	Angular Sensor
Sensor principle	Contact-free, Hall effect
Measuring range	180°
Mechanical end stop	No
Supply voltage	8 – 30 VDC
Current consumption max.	20 mA
Output signal	
Angle /°	Output signal
L (90°)	0,25 VDC
0°	2.5 VDC
R (90°)	4.75 VDC
Delay of the output signal	ca. 3 ms
Reverse polarity protection	Yes
Output	24h short –circuit proof
EMC	200V/m acc. to ISO 11452-3
Ambient conditions	
Operating temperature:	- 40°C bis + 85°C
Temperature range (storage)	- 40°C bis + 125°C
protection class	IP67 acc. to DIN 40050
Tightening torque of the mounting screw max.	2,5 Nm ± 0,5 Nm
Accuracy	±1,6% / 2mV/°
Hysteresis	None
Linearity	± 2°
Cycles of rotation	30 x 10 ⁶ cycles



Pin configuration	
1	GND
2	Ub 5 VDC
3	4.75-0.25 VDC



DESIGN UNITS: MM TOLERANCES UNLESS NOTED: GEOMETRICAL TOLERANCE ACCORDING TO DIN ISO 1101 GENERAL TOLERANCES ACCORDING TO DIN 16901-130B	DRAWN	MBH	18 JUN08	Honeywell					
	CHECK	JLH	18 JUN08						
	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE ANGULAR SENSOR ±90°					
	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE A3	TYPE I	DRAWING NAME RPNS180HD1B11A		REV A	
THIRD ANGLE PROJECTION 	AUTOCAD		2D	SCALE		-	SHEET		1 OF 1