





X (Lochbild) (board drillings)




A-B 2:1




Voreiler / preleading pin 0,8
 Standard / standard pin
 Nacheiler / lagging pin 0,6

Kontakt-Typ
pin-type — A B C




X Kontaktbelegung contact loading



Z 10:1

Querschnitt der
Lötanschlüsse:
cross-section of
solder terminations:



09 73 164 7903	3	Au flash over PdNi over Ni
09 73 164 6903	2	Au flash over PdNi over Ni
09 73 164 2903	1	Au flash over PdNi over Ni
Bestell-Nr. part-no.	Anforderungsstufe nach IEC performance level acc. to IEC	Kontaktoberfläche contact plating

All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances IEC 60603-2	
				Dat.	Name	Maßstab/Scale	
			Detail.	15.01.01	Rie.	1:1	Bauform R Messerleiste Einlot 4,0 , 64pol. type R male connector solder 4,0 , 64pol.
			Insp.	15.01.01	Pa.	2:1	
			Stand.			10:1	
35548	17.07.09	Hage.					TB 09 73 164 x903
34650	17.01.08	Hage.					
28737							
Mod.	Dat.	Name	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP				Blatt/ page
							Sub.