



THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISONS			
GP		00		P	LTR	DESCRIPTION	DATE
				H		REVISED PER ECC-08-007327	27JAN2009
				DIN		APV	
						ZMR/WLM	



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. ALL DIMENSIONS ARE REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
3. MATERIAL:
HOUSING, COVER AND CABLE CLAMP - THERMOPLASTIC (BLACK)
TERMINALS - HIGH STRENGTH COPPER ALLOY PLATED WITH EITHER .000030 MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE .000030 MIN TOTAL, ON MATING SURFACE. .000050 MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
4. COVER AND CABLE CLAMP SHIPPED UNASSEMBLED.
5. WIRE SIZE: 24 & 26 AWG SOLID OR 24 AWG 7 STRANDS OF COPPER CONDUCTOR. MAX INSULATION DIA OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
6. CABLE RANGE: .425 MAX DIA
7. KIT SHIPPED IN POLYBAG FORM.
8. CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF TYCO ELECTRONICS.

AS SHOWN	553912-1
DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN A. HOLT 9-13-82	Tyco Electronics Corporation Harrisburg, PA 17105-3608
		CHK M.D. FRIEL 9-14-82	
		APVD C.F. MORGA 9-15-82	
		NAME	
DIMENSIONS: INCHES		PRODUCT SPEC	KIT, RECEPTACLE 50 POSITION, B SLOT CHAMP-LOK THIN FLANGE
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	
0 PLC ± .005		WEIGHT	
1 PLC ± .005		SIZE CASE CODE DRAWING NO	
2 PLC ± .005		A2 00779	RESTRICTED TO
3 PLC ± .005		© 553912	
4 PLC ± .005		CUSTOMER DRAWING	SCALE NTS SHEET 1 OF 1 REV H
ANGLES ± .005			
FINISH			