

NTE723 Integrated Circuit FM Sound System

Description:

The NTE723 is a monolithic integrated circuit FM detector/limiter and audio preamplifier that requires a minimum of external components for operation. It includes three stages of IF limiting and a differential-peak-detection circuit.

Features:

- Simple detector alignment: one coil
- Sensitivity: 3dB limiting voltage 250 μ V typical at 10.7MHz
- Low harmonic distortion
- Excellent AM rejection 55dB typ. at 10.7MHz
- Internal audio preamplifier

Absolute Maximum Ratings:

Power Supply Current (Pin5) 30mA
 Supply Voltage (Pin5) 12.5V
 Power Dissipation (Note 1), P_D 715mW
 Operating Temperature Range, T_{opr} -40° to +85°C
 Storage Temperature Range, T_{stg} -65° to +150°C
 Lead Temperature (During Soldering, 10sec), T_L +300°C

Note 1. For operation in ambient temperatures above 25°C, the device must be derated based on a 150°C maximum junction temperature and a thermal resistance of 175°C/W junction to ambient.

Electrical Characteristics: (T_A = +25°C unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Static Characteristics						
Supply Current	I ₅	V _{CC} = 8.5V	8.5	15	–	mA
		V _{CC} = 11.2V	–	17.5	–	mA
		V _{CC} = 12.5V	–	19	29	mA
Detector Output Level, High	V ₇		–	6.1	–	V
Detector Output Level, Low	V ₈	V _{CC} = 11.2	–	5.4	–	V
Audio Amplifier Output	V ₁₂		–	5.2	–	V

Electrical Characteristics (Cont'd): ($T_A = +25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Dynamic Characteristics ($V_+ = 11.2\text{V}$, $f_o = 10.7\text{MHz}$, $\Delta f = \pm 75\text{kHz}$, $f_m = 400\text{Hz}$)						
Input Limiting Threshold	$V_{\text{IN(LIM)}}$		–	250	600	μV
AM Rejection	AMR	AM: 1kHz @ 30%, $V_{\text{IN}} = 100\text{mV}$	–	55	–	dB
Recovered AF Voltage (At Pin12)	$V_{\text{O(AF)}}$		–	1.5	–	V
Total Harmonic Distortion	THD		–	1	2	%
Audio Preamplifier						
Voltage Gain	$A_{\text{V(AF)}}$	$V_{\text{IN}} = 100\text{mV}$, $f = 400\text{Hz}$	–	21	–	dB
Total Harmonic Distortion	THD	$V_{\text{OUT}} = 2\text{V}$, $f = 400\text{Hz}$	–	1.5	5.0	%

Pin Connection Diagram

