





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00	H		EC 063C 0209 05	27APR05	BSV JLG
		H1		REVISED PER ECO-09-021826	6JAN10	KK AEG



RECOMMENDED HOLE LAYOUT



SECTION X—X

- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 2 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- 3 OBSOLETE PART NUMBERS
- 4 POSTS: .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 5 POSTS: .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6	OBSOLETE	5	3.200	2.900	29	60	7-103165-6
6	OBSOLETE	5	2.700	2.400	24	50	7-103165-1
		5	2.200	1.900	19	40	6-103165-6
6	OBSOLETE	5	1.900	1.600	16	34	6-103165-3
6	OBSOLETE	5	1.700	1.400	14	30	6-103165-1
		5	1.500	1.200	12	26	5-103165-9
		5	1.400	1.100	11	24	5-103165-8
		5	1.200	.900	9	20	5-103165-6
6	OBSOLETE	5	1.100	.800	8	18	5-103165-5
		5	1.000	.700	7	16	5-103165-4
		5	.900	.600	6	14	5-103165-3
6	OBSOLETE	5	.800	.500	5	12	5-103165-2
6	OBSOLETE	5	.700	.400	4	10	5-103165-1
3	OBSOLETE	4	3.800	3.500	35	72	3-103165-2
3	OBSOLETE	4	3.700	3.400	34	70	3-103165-1
3	OBSOLETE	4	3.600	3.300	33	68	3-103165-0
3	OBSOLETE	4	3.500	3.200	32	66	2-103165-9
3	OBSOLETE	4	3.400	3.100	31	64	2-103165-8
3	OBSOLETE	4	3.300	3.000	30	62	2-103165-7
6	OBSOLETE	4	3.200	2.900	29	60	2-103165-6
6	OBSOLETE	4	3.100	2.800	28	58	2-103165-5
3	OBSOLETE	4	3.000	2.700	27	56	2-103165-4
3	OBSOLETE	4	2.900	2.600	26	54	2-103165-3
3	OBSOLETE	4	2.800	2.500	25	52	2-103165-2
		4	2.700	2.400	24	50	2-103165-1
3	OBSOLETE	4	2.600	2.300	23	48	2-103165-0
3	OBSOLETE	4	2.500	2.200	22	46	1-103165-9
3	OBSOLETE	4	2.400	2.100	21	44	1-103165-8
3	OBSOLETE	4	2.300	2.000	20	42	1-103165-7
		4	2.200	1.900	19	40	1-103165-6
		4	2.100	1.800	18	38	1-103165-5
3	OBSOLETE	4	2.000	1.700	17	36	1-103165-4
6	OBSOLETE	4	1.900	1.600	16	34	1-103165-3
3	OBSOLETE	4	1.800	1.500	15	32	1-103165-2
		4	1.700	1.400	14	30	1-103165-1
3	OBSOLETE	4	1.600	1.300	13	28	1-103165-0
		4	1.500	1.200	12	26	103165-9
		4	1.400	1.100	11	24	103165-8
3	OBSOLETE	4	1.300	1.000	10	22	103165-7
		4	1.200	.900	9	20	103165-6
6	OBSOLETE	4	1.100	.800	8	18	103165-5
		4	1.000	.700	7	16	103165-4
		4	.900	.600	6	14	103165-3
6	OBSOLETE	4	.800	.500	5	12	103165-2
		4	.700	.400	4	10	103165-1

PLATING	C	B	A	NO OF POSN	PART NUMBER
---------	---	---	---	------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN H MOLL 16NOV87
CHK R FIEDT 16NOV87
APVD R FIEDT 16NOV87

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

FLAME RETARDANT
COLOR: BLACK
POSTINGS: BRONZE

SEE TABLE

WEIGHT -

CUSTOMER DRAWING

DWN H MOLL 16NOV87
CHK R FIEDT 16NOV87
APVD R FIEDT 16NOV87

NAME

SIZE CAGE CODE DRAWING NO
A1 00779 C=103165

RESTRICTED TO

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

HEADER ASSY, MOD II, DBL ROW,
.100X.100 C/L, RIGHT ANGLE,
(3) SIDED SHROUD

SCALE 4:1 SHEET 1 OF 1 REV H1