




## 55FB1521-16-7L/7L6-0 Product Details

[Share](#) [Print](#) [Email](#)


55FB1521-16-7L/7L6-0

TE Internal Number: 125867-000

 [Active](#)

### Spec 44, Spec 55 and Spec RCW Wire and Cable

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Cable Type = Spec 55F
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 16 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- [TWO CONDUCTOR CABLE, SHIELDED, JACKETED, FILTER LINE...](#) (PDF, English)

##### Catalog Pages/Data Sheets:

- None Available

##### Product Specifications:

- None Available

##### Application Specifications:

- None Available

##### Instruction Sheets:

- None Available

##### CAD Files:

- None Available

##### Related Products:

- [Tooling](#)

[List all Documents](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- [Cable Type](#) = Spec 55F
- [Cable Style](#) = Primary
- Number of Conductors = 2
- Shield Material = Tin-Plated Copper

##### Electrical Characteristics:

- Voltage Rating (VAC) = 600

##### Body Features:

- Wire Size (AWG/CM) = 16 AWG
- Cable Jacket Color = Black, Violet/Violet with Stripe Components
- Conductor Type = Tin-Plated Copper
- Wire Color = Violet/Violet with Striped Components

##### Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Approved Standards = SAE AS-85485/9, SAE AS-85485/12

##### Conditions for Usage:

- Temperature Range (°C) = 150

##### Operation/Application:

- Application = General Purpose - Lightweight

##### Packaging Features:

- Wire Source = United States

##### Other:

- Brand = Raychem
- Comment = Internal wire sizes 22-10 meets or exceeds all requirements of SAE AS85485/9, less identification.; Product meets or exceeds all requirements of SAE AS85485/12 for 22-14 AWG, less identification.

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

