

# 5 mm Square Surface Mount Miniature Trimmers Multi-Turn Cermet Sealed



## FEATURES

- 0.25 W at 85 °C
- Professional grade
- Wide ohmic range (10  $\Omega$  to 1 M $\Omega$ )
- Low contact resistance variation (1 % or 3  $\Omega$ )
- Small size for optimum packaging density
- Top and side adjust styles
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)










**RoHS**  
COMPLIANT

## LINKS TO ADDITIONAL RESOURCES





The TSM4 trimming potentiometer has been designed for surface mount applications and offers volumetric efficiency 5 mm x 5 mm x 3.7 mm with high performance and stability.

The TSM4 design is suitable for both manual or automatic operation, and can withstand vapor phase and reflow soldering techniques.

| DIMENSIONS in millimeters ( $\pm 0.25$ mm)                                          |                                                                                     |                                                                                      |                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| TSM4 YL<br>(TOP ADJUST)                                                             | TSM4 YJ<br>(TOP ADJUST)                                                             | TSM4 ZL<br>(SIDE ADJUST)                                                             | TSM4 ZJ<br>(SIDE ADJUST)                                                              |
|  |  |  |  |
| RECOMMENDED SOLDERING AREAS                                                         |                                                                                     |                                                                                      |                                                                                       |
|  |  |  |  |

**ELECTRICAL SPECIFICATIONS**

|                                              |                                                                                                                 |
|----------------------------------------------|-----------------------------------------------------------------------------------------------------------------|
| Resistive element                            | Cermet                                                                                                          |
| Electrical travel                            | 11 turns $\pm$ 2                                                                                                |
| Resistance range                             | 10 $\Omega$ to 1 M $\Omega$                                                                                     |
| Standard series                              | 1 - 2 - 5                                                                                                       |
| Tolerance standard                           | $\pm$ 10 %                                                                                                      |
| Power rating                                 | Linear<br>0.25 W at 85 °C<br> |
| Circuit diagram                              |                              |
| Temperature coefficient                      | See Standard Resistance Element table                                                                           |
| Limiting element voltage (linear law)        | 300 V                                                                                                           |
| Contact resistance variation (typical)       | 1 % or 3 $\Omega$                                                                                               |
| End resistance (typical)                     | 1 $\Omega$                                                                                                      |
| Dielectric strength (RMS)                    | 600 V (1 minute)                                                                                                |
| Insulation resistance (500 V <sub>DC</sub> ) | 100 M $\Omega$                                                                                                  |

**MECHANICAL SPECIFICATIONS**

|                             |                              |
|-----------------------------|------------------------------|
| Mechanical travel           | 12 turns $\pm$ 2             |
| Operating torque (max. Ncm) | 1.8                          |
| End stop torque (Ncm)       | Clutch action (2 turns max.) |
| Unit weight (max. g)        | 0.28                         |
| Wiper (actual travel)       | Positioned at approx. 50 %   |

**ENVIRONMENTAL SPECIFICATIONS**

|                   |                       |
|-------------------|-----------------------|
| Temperature range | -65 °C to +150 °C     |
| Sealing           | Sealed container IP67 |
| MSL level         | 1                     |

**SOLDERING RECOMMENDATIONS**Recommended reflow profile 2, see Application Note [www.vishay.com/doc?52029](http://www.vishay.com/doc?52029)

**PERFORMANCES**

| TESTS                        | CONDITIONS                                                                                         | TYPICAL VALUES AND DRIFTS                                                     |
|------------------------------|----------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------|
| Load life                    | 1000 h at rated power<br>90°/30° - ambient temp. +85 °C                                            | Total resistance shift = $\pm 3 \Omega$ or $\pm 3 \%$<br>whichever is greater |
| Humidity moisture resistance | MIL-STD-202 method 106<br>10 cycles of 24 hours constituted<br>with damp heat - cold - vibrations  | Total resistance shift = $\pm 2 \%$<br>Insulation resistance = 10 M $\Omega$  |
| Thermal shock                | 5 cycles                                                                                           | Total resistance shift = $\pm 2 \%$<br>Voltage resistance shift = $\pm 1 \%$  |
| Rotational cycling           | 200 cycles                                                                                         | Total resistance shift = $\pm 3 \Omega$ or $\pm 3 \%$<br>whichever is greater |
| Shock                        | MIL-STD-202 method 213 test condition C,<br>100 g - 6 ms,<br>3 successive shocks in each direction | Total resistance shift = $\pm 1 \%$<br>Voltage resistance shift = $\pm 1 \%$  |
| Vibration                    | MIL-STD-202 method 204,<br>20 g - 3 hours (1 hour per axis)                                        | Total resistance shift = $\pm 1 \%$<br>Voltage resistance shift = $\pm 1 \%$  |

**Note**

- Nothing stated herein shall be construed as a guarantee of quality or durability

**STANDARD RESISTANCE ELEMENT DATA**

| STANDARD<br>RESISTANCE<br>VALUES | LINEAR LAW             |                         |                                 | TYPICAL<br>TCR<br>-55 °C<br>+125 °C |
|----------------------------------|------------------------|-------------------------|---------------------------------|-------------------------------------|
|                                  | MAX. POWER<br>AT 85 °C | MAX. WORKING<br>VOLTAGE | MAX. CURRENT<br>THROUGH ELEMENT |                                     |
| $\Omega$                         | W                      | V                       | mA                              | ppm/°C                              |
| 10                               | 0.25                   | 1.58                    | 158                             | $\pm 100$                           |
| 20                               | 0.25                   | 2.23                    | 112                             |                                     |
| 50                               | 0.25                   | 3.53                    | 77                              |                                     |
| 100                              | 0.25                   | 5.00                    | 50                              |                                     |
| 200                              | 0.25                   | 7.07                    | 35                              |                                     |
| 500                              | 0.25                   | 11.2                    | 22                              |                                     |
| 1K                               | 0.25                   | 15.8                    | 15.8                            |                                     |
| 2K                               | 0.25                   | 22.3                    | 11.2                            |                                     |
| 5K                               | 0.25                   | 35.3                    | 7.1                             |                                     |
| 10K                              | 0.25                   | 50.0                    | 5.0                             |                                     |
| 20K                              | 0.25                   | 70.7                    | 3.5                             |                                     |
| 50K                              | 0.25                   | 112                     | 2.2                             |                                     |
| 100K                             | 0.25                   | 158                     | 1.6                             |                                     |
| 200K                             | 0.25                   | 223                     | 1.12                            |                                     |
| 500K                             | 0.08                   | 300                     | 0.83                            |                                     |
| 1M                               | 0.04                   | 300                     | 0.83                            |                                     |

**MARKING**






Vishay trademark, ohmic value, manufacturing date

The ohmic value is indicated by a 3 figure code, the first two are significant figures, the third one is the multiplier.

Example: 100 = 10  $\Omega$   
 101 = 100  $\Omega$   
 102 = 1000  $\Omega$   
 503 = 50 000  $\Omega$

**PACKAGING** in millimeters

On tape and reel, by 500 pieces for Z version, 250 pieces for YJ version: code TR250, or 200 pieces for YL version.  
In bulk on request (plastic box of 50 pieces): code BO50.

**TSM4 ZL**

**TSM4 ZJ**

**TSM4 YJ**

**TSM4 YL**




**ORDERING INFORMATION** (part number)

|       |   |                      |   |                                                          |   |   |           |   |   |                                                                                                                                         |   |   |                                                         |  |  |  |
|-------|---|----------------------|---|----------------------------------------------------------|---|---|-----------|---|---|-----------------------------------------------------------------------------------------------------------------------------------------|---|---|---------------------------------------------------------|--|--|--|
| T     | S | M                    | 4 | Y                                                        | L | 5 | 0         | 4 | K | R                                                                                                                                       | 0 | 5 |                                                         |  |  |  |
| MODEL |   | STYLE                |   | OHMIC VALUE                                              |   |   | TOLERANCE |   |   | PACKAGING                                                                                                                               |   |   | SPECIAL NUMBER                                          |  |  |  |
| TSM4  |   | YJ<br>YL<br>ZJ<br>ZL |   | From 10 $\Omega$ to 1 M $\Omega$<br>504 = 500 k $\Omega$ |   |   | K = 10 %  |   |   | R10 = reel 500 pieces<br>for ZJ and ZL<br>R05 = reel 250 pieces for YJ<br>and 200 pieces for YL<br>On request<br>B25 = box of 50 pieces |   |   | (If applicable)<br>Given by Vishay<br>for custom design |  |  |  |

**DESCRIPTION** (for information only)

|       |       |       |           |         |           |                |
|-------|-------|-------|-----------|---------|-----------|----------------|
| TSM4  | YL    | 500K  | 10 %      |         | TR        | e3             |
| MODEL | STYLE | VALUE | TOLERANCE | SPECIAL | PACKAGING | LEAD (Pb)-FREE |

**RELATED DOCUMENTS**

**APPLICATION NOTES**

|                                                                   |                                                                        |
|-------------------------------------------------------------------|------------------------------------------------------------------------|
| Potentiometers and Trimmers                                       | <a href="http://www.vishay.com/doc?51001">www.vishay.com/doc?51001</a> |
| Guidelines for Vishay Sfernice Resistive and Inductive Components | <a href="http://www.vishay.com/doc?52029">www.vishay.com/doc?52029</a> |



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.