

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		S1	REVISED PER ECO-11-005140	28MAR11	RK	HMR

1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.


2. MATERIAL: HOUSING – POLYPHEYLENE OXIDE, BLACK. TERMINAL – HIGH STRENGTH COPPER ALLOY PLATED WITH $0.76\mu\text{m}$ [.000030] MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, $0.76\mu\text{m}$ [.000030] MIN TOTAL ON MATING SURFACE. $1.27\mu\text{m}$ [.000050] MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.

3. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.


4. WIRE SIZE: 24 & 26 AWG SOLID OR 24 AWG 7 STRANDS OF COPPER CONDUCTORS. MAX INSULATION DIAMETER OF 1.14[.045] IS ACCEPTABLE FOR MOST APPLICATIONS.

5. CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF AMP.

6. DUST COVER, IF INCLUDED, IS SHIPPED NOT ASSEMBLED.



NO	552032-1
DUST COVER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	DL DRUMMOND	01JUN01	 TE Connectivity			
		CHK	DL DRUMMOND	01JUN01				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	EW BEILES	01JUN01	NAME PLUG ASSEMBLY, 50 POSITION, B-SLOT, BAIL LOCK, CHAMP-LOK	
		0 PLC ± -		PRODUCT SPEC				
		1 PLC ± -		—				
		2 PLC ± -		APPLICATION SPEC				
		3 PLC ± -		—				
		4 PLC ± -						
		ANGLES ± -						
MATERIAL		FINISH		WEIGHT		—		
				A2		00779		
				C=552032				
CUSTOMER DRAWING				SCALE		2:1		
				SHEET		1 of 1		
				REV		S1		