






LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REL PER 0G3A-0619-00	04OCT00	JR	DD
			B1	REVISED PER ECO-09-024606	30OCT09	KK	AFG



- 1 PART ACCEPTS 3.18[.125] BLADE CONTACT
PART NUMBER 1217076-1.
- 2 TWO POSITION CAP WILL HAVE (2) SIX SIDED CAVITIES,
EACH ADDITIONAL POSITION WILL ADD AN EIGHT SIDED CAVITY
BETWEEN THE (2) OUTSIDE CAVITIES.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

3	OBSOLETE	521277-4	10.67[.420]	38.20[1.525]	29.97[1.180]	5	521274-4
		521277-3	10.67[.420]	31.24[1.230]	22.48[.885]	4	521274-3
		521277-2	3.05[.120]	23.75[.935]	14.99[.590]	3	521274-2
		MATES WITH PART NO	DIMENSION C	DIMENSION B	DIMENSION A	NO OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 20JUL00		AMP AMP Incorporated Harrisburg, PA 17105-3608									
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:				CHK MS FEHER 20JUL00							
		0 PLC ±- 1 PLC ±- 2 PLC ±0.25 [.010] 3 PLC ±- 4 PLC ±- ANGLES ±-		APVD D DECKER 20JUL00		NAME							
MATERIAL HEAT STABILIZED NYLON		FINISH COLOR-NATURAL		PRODUCT SPEC -		CAP,3.18 [.125] BLADE							
				APPLICATION SPEC -									
				WEIGHT -									
				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO						
				A200779		C- 521274	-						
CUSTOMER DRAWING								SCALE	2:1	SHEET	1 of 1	REV	B