



ROHS-COMPLIANT

LTR	REV	DESCRIPTION	DATE
 *2	D	ECR # 110817-1 EDIT PACKING LABEL SIZE	08/17/11'



 BAR CODE LABEL 



NOTE:

- 1.CABLE: C1: UL-2725 #28(7/0.127)×1P COLOR: WHITE & GREEN + #28(7/0.127)×2C COLOR: RED & BLACK + AL/MY + SPIRAL(65%)T.C PVC JACKET OD:3.5±0.2mm COLOR:BEIGE(NK-A03) REV USB 2.0
C2: NON-UL #28(7/0.27)×2C INS:SR-PVC ID:1.0±0.05mm + AL/MY + PVC JACKET OD:3.5±0.15mm COLOR:BEIGE(NK-A03) .

2.CONNECTOR:

P1&P3: USB A TYPE (MALE) CONTACT:G/F; SHELL:NI-PLATED .
P2: USB B TYPE (MALE) CONTACT:G/F; SHELL:NI-PLATED .

3.HOOD: P1&P2:MOLDED TYPE,PVC 45P,COLOR:BEIGE(NK-A03) .

P3:MOLDED TYPE,PVC 45P,COLOR:RED(NK-R01) .

4.ELECTRICAL TEST:

- (1)100% OPEN SHORT & MIS WIRE TEST .
- (2)CONTACT RESISTANCE 3 ohm Max .
- (3)INSULATION RESISTANCE 10M ohm Min .

5.PACKING: <1>EACH PC / Maxxtro ZIP BAG(M) + BAR CODE LABEL(86×55mm)




BARCODE:7612320128420

<2>EACH PC / POLYBAG + BAR CODE LABEL 

170-2430-2	<2>
170-2430-1	<1>
DWG	PACKING

PIN OUT



Tolerance Inch M/M			Maxxtro®	
.X	.015	.30	Title USB A/M ×2 - USB B/M POWER CABLE	
.XX	.010	.10		
.XXX	.005	.05		
Draw FANNIE 08/17/11'			Customer P/N: 101276(BB-8040-03)	
Chek Emira 8/17			App'd	Customer T-JPC
Engr			Scale	NONE
			Units	M/M
			Third Angle Projection	
			Dwg No. 170-2430	REV:D Sheet.1/1