

## DM7473

### Dual Master-Slave J-K Flip-Flops with Clear and Complementary Outputs

#### General Description


This device contains two independent positive pulse triggered J-K flip-flops with complementary outputs. The J and K data is processed by the flip-flops after a complete clock pulse. While the clock is low the slave is isolated from the master. On the positive transition of the clock, the data from the J and K inputs is transferred to the master. While the clock is high the J and K inputs are disabled. On the negative transition of the clock, the data from the master is transferred to the slave. The logic states of the J and K inputs must not

be allowed to change while the clock is high. Data transfers to the outputs on the falling edge of the clock pulse. A low logic level on the clear input will reset the outputs regardless of the logic states of the other inputs.

#### Features

- Alternate Military/Aerospace device (5473) is available. Contact a Fairchild Semiconductor Sales Office/Distributor for specifications.

#### Connection Diagram



Order Number 5473DMQB, 5473FMQB, DM5473J, DM5473W or DM7473N  
See Package Number J14A, N14A or W14B

#### Function Table

Inputs				Outputs	
CLR	CLK	J	K	Q	$\bar{Q}$
L	X	X	X	L	H
H	$\neg$	L	L	$Q_0$	$\bar{Q}_0$
H	$\neg$	H	L	H	L
H	$\neg$	L	H	L	H
H	$\neg$	H	H	Toggle	

H = High Logic Level

L = Low Logic Level

X = Either Low or High Logic Level

$\neg$  = Positive pulse data, the J and K inputs must be held constant while the clock is high. Data is transferred to the outputs on the falling edge of the clock pulse.

$Q_0$  = The output logic level before the indicated input conditions were established.

Toggle = Each output changes to the complement of its previous level on each high level clock pulse.

**Absolute Maximum Ratings** (Note 1)

Supply Voltage

7V

Input Voltage

5.5V

Operating Free Air Temperature Range

DM54 and 54

DM74

Storage Temperature Range

–55°C to +125°C

0°C to +70°C

–65°C to +150°C

**Recommended Operating Conditions**

Symbol	Parameter	DM5473			DM7473			Units
		Min	Nom	Max	Min	Nom	Max	
$V_{CC}$	Supply Voltage	4.5	5	5.5	4.75	5	5.25	V
$V_{IH}$	High Level Input Voltage	2			2			V
$V_{IL}$	Low Level Input Voltage			0.8			0.8	V
$I_{OH}$	High Level Output Current			–0.4			–0.4	mA
$I_{OL}$	Low Level Output Current			16			16	mA
$f_{CLK}$	Clock Frequency (Note 6)	0		15	0		15	MHz
$t_W$	Pulse Width (Note 6)	Clock High	20		20			ns
		Clock Low	47		47			
		Clear Low	25		25			
$t_{SU}$	Input Setup Time (Notes 2, 6)	0↑			0↑			ns
$t_H$	Input Hold Time (Notes 2, 6)	0↓			0↓			ns
$T_A$	Free Air Operating Temperature	–55		125	0		70	°C

**Note 1:** The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

**Electrical Characteristics**

over recommended operating free air temperature range (unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ (Note 3)	Max	Units
$V_I$	Input Clamp Voltage	$V_{CC} = \text{Min}$ , $I_I = -12 \text{ mA}$			–1.5	V
$V_{OH}$	High Level Output Voltage	$V_{CC} = \text{Min}$ , $I_{OH} = \text{Max}$ $V_{IL} = \text{Max}$ , $V_{IH} = \text{Min}$	2.4	3.4		V
$V_{OL}$	Low Level Output Voltage	$V_{CC} = \text{Min}$ , $I_{OL} = \text{Max}$ $V_{IH} = \text{Min}$ , $V_{IL} = \text{Max}$		0.2	0.4	V
$I_I$	Input Current @ Max Input Voltage	$V_{CC} = \text{Max}$ , $V_I = 5.5 \text{ V}$			1	mA
$I_{IH}$	High Level Input Current	$V_{CC} = \text{Max}$ $V_I = 2.4 \text{ V}$	J, K		40	$\mu\text{A}$
			Clock		80	
			Clear		80	
$I_{IL}$	Low Level Input Current	$V_{CC} = \text{Max}$ $V_I = 0.4 \text{ V}$	J, K		–1.6	mA
			Clock		–3.2	
			Clear		–3.2	
$I_{OS}$	Short Circuit Output Current	$V_{CC} = \text{Max}$ (Note 4)	DM54	–20	–55	mA
			DM74	–18	–55	
$I_{CC}$	Supply Current	$V_{CC} = \text{Max}$ , (Note 5)		18	34	mA

**Note 2:** The symbol (↑, ↓) indicates the edge of the clock pulse is used for reference: (↑) for rising edge, (↓) for falling edge.

**Note 3:** All typicals are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

**Note 4:** Not more than one output should be shorted at a time.


**Note 5:** With all outputs open,  $I_{CC}$  is measured with the Q and  $\bar{Q}$  outputs high in turn. At the time of measurement the clock input grounded.

**Note 6:**  $T_A = 25^\circ\text{C}$  and  $V_{CC} = 5 \text{ V}$ .


## Switching Characteristics

at  $V_{CC} = 5V$  and  $T_A = 25^\circ C$



Symbol	Parameter	From (Input) To (Output)	$R_L = 400\Omega$ $C_L = 15\text{ pF}$		Units
			Min	Max	
$f_{MAX}$	Maximum Clock Frequency		15		MHz
$t_{PHL}$	Propagation Delay Time High to Low Level Output	Clear to Q		40	ns
$t_{PLH}$	Propagation Delay Time Low to High Level Output	Clear to $\bar{Q}$		25	ns
$t_{PHL}$	Propagation Delay Time High to Low Level Output	Clock to Q or $\bar{Q}$		40	ns
$t_{PLH}$	Propagation Delay Time Low to High Level Output	Clock to Q or $\bar{Q}$		25	ns



## Physical Dimensions inches (millimeters) unless otherwise noted




**14-Lead Ceramic Dual-In-Line Package (J)**  
**Order Number 5473DMQB or DM5473J**  
**Package Number J14A**



**14-Lead Molded Dual-In-Line Package (N)**  
**Order Number DM7473N**  
**Package Number N14A**

# Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**Fairchild Semiconductor Corporation Americas**  
 Customer Response Center  
 Tel: 1-888-522-5372

**Fairchild Semiconductor Europe**  
 Fax: +49 (0) 1 80-530 85 86  
 Email: europe.support@nsc.com  
 Deutsch Tel: +49 (0) 8 141-35-0  
 English Tel: +44 (0) 1 793-85-68-56  
 Italy Tel: +39 (0) 2 57 5631

**Fairchild Semiconductor Hong Kong Ltd.**  
 13th Floor, Straight Block,  
 Ocean Centre, 5 Canton Rd.  
 Tsimshatsui, Kowloon  
 Hong Kong  
 Tel: +852 2737-7200  
 Fax: +852 2314-0061

**National Semiconductor Japan Ltd.**  
 Tel: 81-3-5620-6175  
 Fax: 81-3-5620-6179

[www.fairchildsemi.com](http://www.fairchildsemi.com)