


PRODUCT NO.
72206-000CA/000CALF
NOTE ⑧




NOTES:

- 1 8mm MIN CARD EJECT.
- 2 PUSH-ROD TRAVEL: 9.5mm
- 3 MATERIAL:
 - 3.1 HEADER ASSY:
PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK - ABOVE PCB
PIN: PHOSPHOR BRONZE
 - 3.2 EJECT MECHANISM ASSY:
PLASTIC GUIDE: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PLASTIC PUSH-ROD BUTTON: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
COVER PLATE, EJECT PLATE, LINK ARM,
PUSH ROD: STAINLESS STEEL
EMI CONTACT: PHOSPHOR BRONZE
- 4 FINISH (PIN)
UNDER PLATING: 0.5um MIN Ni
CONTACT AREA: 0.076 um MIN. GOLD

SOLDER TAIL: 2.5umMIN Sn-Pb FOR TIN LEAD OPTION
2.5umMIN PURE TIN FOR LEAD FREE OPTION
- ⑤ DIM "X"

4.25±0.1	3.5±0.1	5.0±0.1
OTHERS	36,67	1,17,34,35,51,68
- 6 RECOMMENDED HOLD DOWN - 2mm SCREWS (95121-001) AND NUTS (92869-001).
RECOMMENDED SCREW TORQUE: 1.0 TO 1.5 MAX in-lbs. (1.2-1.7 cm-kgs).
- 7 SEE SHEET 3 FOR PCB LAYOUT INFORMATION.
- ⑧ ADD "H" TO PART NUMBER FOR OPTIONAL HOLD DOWN (2 PER EJECT MECHANISM).






HOLD DOWN


- 9 IF LEAD FREE P/N.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- 10 IF LEAD FREE P/N.THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCIBLED IN GS-22-008
- 11 LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- 12 PRODUCT SPEC:110-263

mat'l. code				surface		tolerance		projection		product family			
				ISO1302		ISO1101 ISO406		MM		MCS			
l t r e c n n o d r				date		tolerances unless otherwise specified		MM		R/A CARDBUS SINGLE DECK ASSEMBLY			
E	V12164	TFG	8/16/01			0.X±0.3							
F	N05-0054	WB	03/02/05			0.XX±0.13							
G	EX-N-011408	ZK	04/02/12			0.XXX±0.051		scale 1:1					
				dr		R.GRAPE		4/29/96		dwg no			
				engr		D.BRANN		4/29/96		sheet 1 of 3			
				chr		D.BRANN		4/29/96		72206			
				appd		D.BRANN		4/29/96		A4			
sheet				revising		G		G		type			
index				sheet		1		2		Product Customer Drawing			


PRODUCT NO.
72206-100CA/100CALF
NOTE ③



mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection MM	product family MCS
ltr ecn nodr date	tolerances unless otherwise specified	angle 0°±2'	scale 1:1	R/A CARDBUS SINGLE DECK ASSEMBLY
				dwg no 72206
	dr R.GRAPE 4/29/96	engr D.BRANN 4/29/96	chr D.BRANN 4/29/96	appd D.BRANN 4/29/96
sheet index	revision sheet			type Product Customer Drawing



P.C.B. LAYOUT



NOTES:

- ① RECOMMENDED DIAMETER IS $\phi 1.0$. FOR PROCESSES USING PASTE REFLOW, HOLE MAY BE AS SMALL AS $\phi 0.79$.
- 2 ALL TOLERANCES ± 0.15 UNLESS NOTED.

mat'l. code		surface	tolerance	projection	product family
ISO1302		ISO1101	ISO406		MCS
ltr ecn nodr	date	tolerances unless otherwise specified		title	
G		angle	$0.X \pm 0.3$	MM	R/A CARDBUS SINGLE DECK ASSEMBLY
			$0.XX \pm 0.13$		
		$0^\circ \pm 2'$	$0.XXX \pm 0.051$	scale 1:1	
		dr	R.GRAPE	4/29/96	dwg no 72206 sheet 3 of 3 size A4
		enr	D.BRANN	4/29/96	
		chr	D.BRANN	4/29/96	
		appd	D.BRANN	4/29/96	type Product Customer Drawing
sheet index	revision sheet				