




CIRCUIT No. 1
SEE NOTE 4




1.14 REF. ROUND OR SQUARE PIN.



SECTION A-A




HOUSING OPTION
WITH RAMP
91813-91**



CIRCUIT No. 1
SEE NOTE 4

12	91813-9012	91813-9112	55.88	±0.25	60.96	±0.25
11	↑ -9011	↑ -9111	50.80	±0.20	55.88	±0.25
10	↑ -9010	↑ -9110	45.72	±0.20	50.80	±0.25
9	↑ -9009	↑ -9109	40.64	±0.20	45.72	±0.25
8	↑ -9008	↑ -9108	35.56	±0.20	40.64	±0.25
7	↑ -9007	↑ -9107	30.48	±0.20	35.56	±0.25
6	↑ -9006	↑ -9106	25.40	±0.10	30.48	±0.25
5	↑ -9005	↑ -9105	20.32	±0.10	25.40	±0.25
4	↑ -9004	↑ -9104	15.24	±0.10	20.32	±0.25
3	↑ -9003	↑ -9103	10.16	±0.10	15.24	±0.25
2	91813-9002	91813-9102	5.08	±0.10	10.16	±0.25
O.K.T. SIZE	PART NO. WITHOUT RAMP	PART NO. WITH RAMP	DIMENSION			



SECTION B-B

NOTE:

1. MATERIAL: POLYAMIDE (PA6), UL-94V-2
COLOR: WHITE
2. FINISH: N/A
3. PRODUCT SPECIFICATION: PS-99020-0087
4. CIRCUIT 1 MAY OR MAY NOT LINE UP WITH CIRCUIT 1 OF THE MATING PART.
5. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
6. THIS HOUSING USES KK TERM. No's. 2478, 2578 & 2878.
7. COLOUR VARIATION MAY BE VISIBLE ON THE HOUSING SURFACES.

OBSOLETE 13-20CKT EC NO: UCP2011-0476 DRWN:KIPPER 2010/12/03 CHKD:JBELL APPR:FSMITH 2010/12/06	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 7:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY DWASZKIEWICZ	DATE 2006/06/08	TITLE 5.08MM KK CRP TERM HSG GLOW WIRE COMPATIBLE		
			4 PLACES	± ---	± ---	CHECKED BY	DATE			
			3 PLACES	± ---	± ---	J.DENNEHY				
			2 PLACES	± 0.25	± ---	APPROVED BY	DATE	MOLEX INCORPORATED		
			1 PLACE	± 0.35	± ---	FSMITH	2010/12/06			
			ANGULAR ±1/2°			MATERIAL NO.		DOCUMENT NO.		SHEET NO.
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		SD-91813-001		1 OF 1			
			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					