

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
		K		REV PER 0G3A-0582-04	31AUG04	JR TM

AMP
WIRE RANGE24-20 AWG
STRANDED

- 1 WIRE INSULATION DIA 1.02 [.040] TO 2.54 [.100].
- 2 FINISH: BODY AND SLEEVE: TIN/LEAD (93-7) PLATE PER ASTM B545. (3% MIN LEAD CONTENT)
- 3 MATERIAL: BODY AND SLEEVE, COPPER PER ASTM B152
INSULATION: PVF²
COLOR- NATURAL



M7928/6-2 CLASS 2	2500	ON TAPE	53547-2
M7928/6-2 CLASS 1 & 2	1000	LOOSE PIECE	53547-1
MILITARY PART NUMBER & CLASS PER MIL-T-7928	QTY	PACKAGE TYPE	PART NO.


AMP INCORPORATED
CUSTOMER SERVICE SYSTEMSMAX RECOMMENDED OPERATING
TEMPERATURE:
150°C

THIS DRAWING IS A CONTROLLED DOCUMENT.

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.VOLTAGE RATING:
-CIRCULAR MIL AREA:
0.16-0.65mm² [202-1,290]
STRANDEDDIMENSIONS:
MM [INCHES]

MATERIAL

- 3

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± 0.20 [.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH - 2

DWN S.S. GOULDEN 9-28-93

CHK R. HERSEY 9-28-93

APVD M ELLIS 9-28-93

PRODUCT SPEC

108-11023

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, Pa 17105-3608NAME
SPLICE, BUTT, PVF², P.I.D.G.
WIRE SIZE: 24-20 AWG

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-53547

SCALE 1:1 SHEET 1 OF 1 REV K