

Dual Chip, Right Angle 3 Leads, Black Epoxy - High Ic

INDEX

PRODUCT TREE



SPEC! Image next to part no. indicates cad file.

- [Product Table](#)
- [Table Footnotes](#)
- [Order Samples](#)
- [Stock/Price Request](#)
- [Sales and Tech Support](#)

1. [Product Gallery](#)
2. [Opto-Electronic Components](#)
3. [Phototransistors](#)
4. [Side Sensing/Right Angle Phototransistors](#)
5. [Dual Chip, Right Angle 3 Leads, Black Epoxy - High Ic](#)

Lumex drawings are in PDF format. If you don't have Adobe Acrobat, click on this icon to

[download a free copy](#)



Lumex Part Number	Lens	Vceo (V) Max *	PC (mW) Max *	t-opr (deg C) *	Iceo @ 10 Vceo (nA) Max	Ic (mA) Min **	Ic (mA) Typ **	Ic (mA) Max **	Vce (V) **	lambda p (nm) Typ.	delta theta deg Typ.	lambda (nm)	tr/tf @ Vec 5V Ic 1ma
OED-ST-392T SPEC!	Black Epoxy	30	75	- 20 ; + 70	100	0.8	-	-	10	900	+/- 60	600 ; 1050	15/15 mS

Table Footnotes

[\[top of page\]](#)

- * Limits of Safe Operation
- ** @ EV ~ 1000 Lx

290 East Helen Road Palatine, IL 60067 Telephone: (847) 359-2790 Facsimile: (847) 359-8904 E-mail us at sales@lumex.com

© 1997-2001 Lumex, Inc.