

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

171692-0102

Status:

Active

Overview:

Mega-Fit® Power Connectors

Description:

Mega-Fit™ Receptacle Housing, Dual Row, 2 Circuit, UL 94 V-0, Bag

Documents:

3D Model

Drawing (PDF)

Product Specification PS-76823-100 (PDF)

Application Specification AS-76823-100 (PDF)

Test Summary TS-170001-001 (PDF)

Test Summary TS-76823-100 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

UPC

Crimp Housings

171692

Power, Wire-to-Board, Wire-to-Wire

Mega-Fit® Power Connectors

Mega-Fit™

887191246840

Physical

Circuits (maximum)

Circuits Detail

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Temperature Range - Operating

2

2

Black

94V-0

Male

No

Yes

PBT

1.530/g

2

Bag

No

5.70mm

5.70mm

Yes

-40°C to +120°C

Electrical

Current - Maximum per Contact

23A

Material Info

Reference - Drawing Numbers

Application Specification

Product Specification

Sales Drawing

Test Summary

AS-76823-100

PS-76823-100

SD-171692-0100

TS-170001-001, TS-76823-100




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

171692Series

Mates With

Mega-Fit™ Header [76825](#) , [76829](#) , [172064](#) , [172065](#)

Use With

Mega-Fit™ Crimp Terminals, [172063](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[171692-0102](#)