

# FPM-3170G

# FPM-3171G

**17" SXGA Industrial Monitor with Resistive Touchscreen, Direct-VGA, DVI, Video and S-Video Ports**

**17" SXGA Industrial Monitor with Resistive Touchscreen and Direct-VGA Port**



## Features

- 17" SXGA TFT LCD with resolution up to 1280 x 1024
- Robust design with stainless steel chassis and aluminum front panel
- Anti-reflective screen with tempered glass
- Supports stainless steel front panel (optional)
- OSD control pad on front panel
- Supports industrial 24-48 V<sub>DC</sub> power input (optional)
- Supports transreflective LCD technology (optional)
- Supports Panel, Wall, Desktop, Rack or VESA arm mounting
- Front panel NEMA4/IP65 compliant

## Introduction

FPM-3170G is a 17" color TFT LCD flat panel monitor specifically designed for industrial applications. With a viewing size as large as 17", it presents an ample display area as well as vivid and sharp images for your HMI. It features direct VGA signal transmission. You can thus upgrade the displays without making changes to the existing system. The onscreen display function also makes it easy to adjust the images on the screen. The whole chassis is designed in stainless steel and the front panel is made of aluminum with front panel NEMA4/IP65 compliance.

## Specifications

### General

- **Button Controls** OSD (Onscreen Display) control pad on front panel
- **Certification** BSMI, CCC, CE, FCC
- **Dimension (W x H x D)** 482 x 354 x 68 mm (18.9" x 13.9" x 2.7")
- **Enclosure** Front panel: Aluminum with coating,  
Rear cover: Stainless steel chassis
- **Mounting** Panel, wall, desktop, VESA arm & 19" rackmount
- **Power Input** External 50 W power adapter, with AC 100 V ~ 240 V input and DC +12 V @ 4.16 A output
- **Video Port** FPM-3170G: VGA, DVI-D, S-Video, Video  
FPM-3171G: Direct - VGA
- **Weight (Net)** 9.25 kg (20.39 lbs)

### LCD Display

- **Display Type** SXGA TFT LCD
- **Display Size** 17"
- **Max. Resolution** 1280 x 1024
- **Max. Color** 16.2 M
- **Viewing Angle (H, V)°** 140, 130
- **Luminance (cd/m<sup>2</sup>)** 300
- **Backlight Life (hrs)** 40,000
- **Contrast Ratio** 700 : 1

### Touchscreen (Optional)

- **Sensor** ELO
- **Type** 5-wire Resistive
- **Interface** RS-232 or USB
- **Lifespan** 35 million touches at a single point
- **Light Transmission** 80% ±5
- **OS Support** DOS, Windows® 95/98/ME/2000/XP/NT
- **Power Consumption** +5 V @ 100 mA
- **Touch Resolution** Linearity

### Environment


- **Operation Temperature** 0 ~ 50° C (32 ~ 122° F)
- **Storage Temperature** -20 ~ 60° C (-4 ~ 140° F)
- **Humidity (Storage)** 10 ~ 95% non-condensing
- **Waterproof** Front Panel NEMA4/IP65 Compliant
- **Vibration** 5 ~ 500 Hz, 1 Grms (Operating, Random)

## Ordering Information

- **FPM-3170G-XBE** 17" Industrial Monitor with D-VGA, DVI-D, S-V, Video ports
- **FPM-3170G-RBE** FPM-3170G-XBE w/Resistive TS (RS-232 interface)
- **FPM-3170G-UBE** FPM-3170G-XBE w/Resistive TS (USB Interface)
- **FPM-3171G-XBE** 17" Industrial Monitor with Direct VGA port
- **FPM-3171G-RBE** FPM-3171G-XBE w/Resistive TS (RS-232 Interface)
- **FPM-3171G-UBE** FPM-3171G-XBE w/Resistive TS (USB Interface)
- **PWR-246E** Ind. DC to DC Converter w/24-48 V<sub>DC</sub> Power Input

## Dimensions

**Unit: mm**




Cut out dimension 451 x 333 mm (17.75" x 13.38")

Diameters of the rackmount holes:

Vertical: 6.5 mm


Horizontal: 9 mm



## Accessories


- **1702002600** Power Cable US Plug 1.8 M
- **1702002605** Power Cable EU Plug 1.8 M
- **1702031801** Power Cable UK Plug 1.8 M
- **1702031836** Power Cable China/Australia Plug 1.8 M

## Mounting with DC Source




## I/O View

**FPM-3170G**



**FPM-3171G**



## Rear View

