

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

FT

0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D5	REVISED PER ECO-11-004820	11MAR2011	RK	HMR

TEST FACILITY

CLAMPING SCREW

0.5

INTERLOCKING FEATURE

282856-3 AS SHOWN

2.60

3.50

2.5 REF

A

WIRE ENTRY

1.0±0.1

5.0±0.2

7

10.0

19.0

B

0.80±0.05

5.0±0.2

RECOMMENDED PC BOARD LAYOUT

Ø 1.4^{+0.1}₋₀

5.0

Ø 0.1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.3

1 PLC ±.25

2 PLC ±.25

3 PLC ±.

4 PLC ±.

ANGLES ±2

MATERIAL

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

23AUG2001

23AUG2001

23AUG2001

108-20166

114-20079

-

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

TERMINAL BLOCK PCB MOUNT

SIDE ENTRY WIRE, STACKING

W/INTERLOCK, 5mm PITCH

A300779

C-282856

-

SCALE

SHEET

OF

REV

3:1

1

2

D5

	BLACK	7.0	10	2	2-282856-8
8	GREEN	7.0	10	2	2-282856-7
8		4.5	10	2	2-282856-6
		3.5	125	25	2-282856-5
		3.5	120	24	2-282856-4
		3.5	115	23	2-282856-3
		3.5	110	22	2-282856-2
		3.5	105	21	2-282856-1
		3.5	100	20	2-282856-0
		3.5	95	19	1-282856-9
		3.5	90	18	1-282856-8
		3.5	85	17	1-282856-7
		3.5	80	16	1-282856-6
		3.5	75	15	1-282856-5
		3.5	70	14	1-282856-4
		3.5	65	13	1-282856-3
		3.5	60	12	1-282856-2
		3.5	55	11	1-282856-1
		3.5	50	10	1-282856-0
		3.5	45	9	282856-9
		3.5	40	8	282856-8
		3.5	35	7	282856-7
		3.5	30	6	282856-6
		3.5	25	5	282856-5
		3.5	20	4	282856-4
		3.5	15	3	282856-3
	GREEN	3.5	10	2	282856-2
	COLOR	DIM. B	DIM. A	N° OF POS.	PART NUMBER

4

3

2

1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		-	SEE SHEET 1	-	-	-



MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR SEE TABLE.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.


- 2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3 END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.
- 4 WIRE SIZE RANGE
SOLID WIRE: 0,03-4mm² (11AWG).
STRANDED WIRE: 0,03-2,5mm² (13AWG).
- 5 RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE N° E60677.
- 6 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.



NOT CUMULATIVE TOLERANCE.



PRELIMINARY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 23AUG2001	 TE Connectivity																	
DIMENSIONS: mm		CHK D. BIEVENOUR 23AUG2001	NAME TERMINAL BLOCK PCB MOUNT SIDE ENTRY WIRE, STACKING W/INTERLOCK, 5mm PITCH																	
		APVD D. BIEVENOUR 23AUG2001																		
<table><tr><td colspan="2">TOLERANCES UNLESS OTHERWISE SPECIFIED:</td></tr><tr><td>0 PLC</td><td>±-</td></tr><tr><td>1 PLC</td><td>±.2</td></tr><tr><td>2 PLC</td><td>±.15</td></tr><tr><td>3 PLC</td><td>±-</td></tr><tr><td>4 PLC</td><td>±-</td></tr><tr><td>ANGLES</td><td>±2</td></tr></table>		TOLERANCES UNLESS OTHERWISE SPECIFIED:		0 PLC	±-	1 PLC	±.2	2 PLC	±.15	3 PLC	±-	4 PLC	±-	ANGLES	±2	PRODUCT SPEC -	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:																		
		0 PLC	±-																	
		1 PLC	±.2																	
2 PLC	±.15																			
3 PLC	±-																			
4 PLC	±-																			
ANGLES	±2																			
APPLICATION SPEC -																				
MATERIAL -		WEIGHT -	A300779C-282856			-														
		CUSTOMER DRAWING																		
		SCALE 3:1		SHEET 2 OF 2		REV D5														