

AC POWER LINE TVS COMPONENT

APPLICATIONS

- ✓ AC Power Mains
- ✓ Module Lightning Protection

IEC COMPATIBILITY (EN61000-4)


- ✓ 61000-4-5 (Power): 8/20 μ s - 1kA, L4 (Line-Line), 333A, L4 (Line-Ground)

FEATURES


- ✓ 4784 to 6920 Kilowatts Peak Pulse Power per Line (8/20 μ s)
- ✓ Glass Passivated Chip
- ✓ Bidirectional Configuration
- ✓ Easy Mounting to Printed Circuit Boards
- ✓ Available in Voltage Types Ranging From: 90V to 240VAC

MECHANICAL CHARACTERISTICS

- ✓ Epoxy Case
- ✓ Weight 7.2 - 11.3 grams (Approximate)
- ✓ Flammability Rating UL 94V-0
- ✓ Marking: Logo & Device Marking Code



APPLICATION






PAC-95 thru PAC-240

DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power Dissipation ($t_p = 8/20\mu s$) - See Fig. 1	P_{PP}	4784 & 6920	kilowatts
Storage Temperature	T_{STG}	-40 to +125	$^{\circ}C$
Operating Temperature	T_J	-40 to +125	$^{\circ}C$

ELECTRICAL CHARACTERISTICS							
PART NUMBER	RATED STAND-OFF VOLTAGE		BREAKDOWN VOLTAGE		MAXIMUM LEAKAGE CURRENT @ V_{WM} I_D μA	MAXIMUM CLAMPING VOLTAGE @ 8/20 μs V_C @ I_{PP}	TEMPERATURE COEFFICIENT OF $V_{(BR)}$ $\theta V_{(BR)}$ %/ $^{\circ}C$
	V_{WM} VOLTS AC	V_{WM} VOLTS DC	MIN $V_{(BR)}$ VOLTS DC	@ I_T mA			
PAC-95	95	135	157	1	20	299V @ 16kA	0.1
PAC-130	130	202	214	1	20	378V @ 16kA	0.1
PAC-240	240	380	400	1	20	692V @ 10kA	0.1


GRAPHS



PAC-95 thru PAC-240

PACKAGE OUTLINE & DIMENSIONS


90VAC RADIAL LEAD PACKAGE OUTLINE



PACKAGE DIMENSIONS (90 VAC Device)

DIM	MILLIMETERS	INCHES
	(Nominal)	(Nominal)
A	12.5	0.49
B	12.45	0.49
C	1.27	0.05
D	20.1	0.79
E	6.35	0.25
F	23.37	0.92

130 & 240 VAC RADIAL LEAD PACKAGE OUTLINE



PACKAGE DIMENSIONS (130 & 240 VAC Devices)

DIM	MILLIMETERS	INCHES
	(Nominal)	(Nominal)
A	18.12	0.69
B	13.72	0.54
C	1.25	0.049
D	23.722 ± 1.16	0.934 ± 0.046
E	7.37	0.29
F	20.0	0.787

06041 Rev 0 - 2/03

ProTek Devices
2929 South Fair Lane, Tempe, AZ 85282
Tel: 602-431-8101 Fax: 602-431-2288
E-Mail: sales@protekdevices.com
Web Site: www.protekdevices.com

COPYRIGHT © ProTek Devices 2003

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.