






FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE NOTE 1



mat'l. code				surface		tolerance		projection	product family				
NOTE 3				ISO 1302 ✓		ISO 406 ISO 1101			HPC				
ltr	ecr no	dr	date	tolerances unless otherwise specified					title				
E	v40285	PCP	1/20/94	angles		linear			4 ROW VERTICAL HEADER W/PRESS FIT PINS, 1 G.P.				
F	v40941	PCP	6/01/94										
G	v82253	HTB	12/28/98	0°±2'		.XXX ±.005/.13 .XXXX ±.0020/.051		INCH/MM		scale 1:1			
H	v00271	JWS	1/31/00	dr	D. SHEAFFER		3/14/91			dwg no		sheet 1 of 4	size
J	v05-0758	DAI	9/12/05	enr	S. CLARK		3/14/91			50010		A3	
K	v05-1039	DAI	11/11/05	chr	S. CLARK		3/14/91			type Product Customer Drawing			
L	M06-0261	AEA	7/08/06	appd	S. CLARK		3/14/91						
sheet		revision		L	L	L	L						
index		sheet		1	2	3	4						



form: A3



FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE NOTE 1



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100/2.54 GRID
UNLESS OTHERWISE SPECIFIED)

mat'l. code NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecm	no	dr	date	tolerances unless otherwise specified	scale 1:1 FCI	title 4 ROW VERTICAL HEADER W/PRESS FIT PINS, 1 G.P.
L					angles linear .XX ±.01/.3		
					.XXX ±.005/.13		
					0°±2' .XXX ±.0020/.051		
			dr	D. SHEAFFER	3/14/91		dwg no
			enr	S. CLARK	3/14/91		sheet 2 of 4 size
			chr	S. CLARK	3/14/91		50010 A3
			appd	S. CLARK	3/14/91		type Product Customer Drawing
sheet index	revision sheet						

form: A3

PDM: Rev:L **STATUS: Released** Printed: May 13, 2011

Copyright FCI

PRODUCT NO.	NO. OF POSITIONS SEE NOTE 2	TAIL LENGTH ±.015/0.38	TERMINAL PLATING	MATING LENGTH
50010 -1YYYA	YYY	.177/4.50	30μ"/0.76μ GOLD	.220[5.59]
50010 -1YYYC	YYY	.533/13.54	30μ"/0.76μ GOLD	
50010 -1YYYD	YYY	.733/18.62	30μ"/0.76μ GOLD	
50010 -1YYYG	YYY	.250/6.35	30μ"/0.76μ GOLD	
50010 -1YYYL	YYY	.188/4.78	30μ"/0.76μ GOLD	
50010 -1YYYP	YYY	.470/11.94	30μ"/0.76μ GOLD	
50010 -3YYYA	YYY	.177/4.50	50μ"/1.27μ GOLD	
50010 -3YYYC	YYY	.533/13.54	50μ"/1.27μ GOLD	
50010 -3YYYD	YYY	.733/18.62	50μ"/1.27μ GOLD	
50010 -3YYYG	YYY	.250/6.35	50μ"/1.27μ GOLD	
50010 -3YYYL	YYY	.188/4.78	50μ"/1.27μ GOLD	
50010 -3YYYP	YYY	.470/11.94	50μ"/1.27μ GOLD	
50010 -5YYYA	YYY	.177/4.50	30μ"/0.76μ GXT	
50010 -5YYYALF	YYY	.177/4.50	30μ"/0.76μ GXT	
50010 -5YYYC	YYY	.533/13.54	30μ"/0.76μ GXT	
50010 -5YYYCLF	YYY	.533/13.54	30μ"/0.76μ GXT	
50010 -5YYYD	YYY	.733/18.62	30μ"/0.76μ GXT	
50010 -5YYYDLF	YYY	.733/18.62	30μ"/0.76μ GXT	
50010 -5YYYG	YYY	.250/6.35	30μ"/0.76μ GXT	
50010 -5YYYGLF	YYY	.250/6.35	30μ"/0.76μ GXT	
50010 -5YYYL	YYY	.188/4.78	30μ"/0.76μ GXT	
50010 -5YYYLLF	YYY	.188/4.78	30μ"/0.76μ GXT	
50010 -5YYYP	YYY	.470/11.94	30μ"/0.76μ GXT	
50010 -5YYYPLF	YYY	.470/11.94	30μ"/0.76μ GXT	.220[5.59]
50010 -XX009	368	SEE SHEET 3	30μ"/0.76μ GXT	SEE SHEET 3
50010 -XX009LF	368	SEE SHEET 3	30μ"/0.76μ GXT	SEE SHEET 3

NOTES:

①. PRODUCT NUMBERING CODE:

50010 - X YYY Z LF

LEAD FREE (OPTIONAL), SEE NOTE 9
TAIL LENGTH, SEE TABLE
NO. OF POSITIONS, SEE NOTE 2
PLATING, SEE TABLE
BASE NUMBER

PRODUCT NUMBERING CODE FOR SELECT LOAD:

50010 - XXYYY LF

LEAD FREE (OPTIONAL) SEE NOTE 9
SEQUENCE NUMBER
ALWAYS 'XX'
BASE NUMBER

②. THIS PRODUCT IS CONFIGURED IN SIZES OF 20 thru 122 COLUMNS IN INCREMENTS OF TWO.
i.e.: 20,22,24,26,.....118,120,122.

③. HOUSING MATERIAL: GLASS AND MINERAL FILLED
HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER
UL94V-0. COLOR: BLACK.
PIN MATERIAL: PHOS BRONZE

④. LENGTH FORMULAS
DIM "A" .100/2.54 x NO. OF COLUMNS +1.05/26.7
DIM "B" .100/2.54 x NO. OF COLUMNS +.750/19.05
DIM "C" .100/2.54 x NO. OF COLUMNS DIVIDED BY 2 -.100/2.54

⑤. Ø.0453/1.151 DRILLED HOLE PLATED WITH .0003/.007 MIN.
SnPb OVER .001/.03 to .003/.08 Cu. PLATING TO ACHIEVE
A Ø.040±.003/1.02±.08 HOLE.

⑥. TO ASSURE PROPER INSTALLATION: TOOLING, AS
SPECIFIED IN INSTRUCTION MANUAL 155915-001 MUST
BE USED. PIN MATING LENGTH WILL BE ±.002/.05
AFTER INSTALLATION.

⑦. COMPANY NAME, PART NUMBER AND LOT CODE TO APPEAR ON
THIS SURFACE PER BUS-12-108.

⑧. REFERENCE 50808 FOR F.M.L.B. AVAILABLE OPTIONS
AND WORKSHEET.

⑨. THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

10. THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE
FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

mat'l. code NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family HPC		
ltr	ecn	no	dr	date	tolerances unless otherwise specified				title			
L					angles	linear	.XX ±.01/.3	INCH/MM		4 ROW VERTICAL HEADER		
					0°±2°		.XXX ±.005/.13			W/PRESS FIT PINS, 1 G.P.		
							.XXXX ±.0020/.051	scale 1:1		dwg no		
					dr	D. SHEAFFER	3/14/91			sheet 4 of 4 size		
				enrg	S. CLARK	3/14/91	50010			A3		
				chr	S. CLARK	3/14/91						
				appd	S. CLARK	3/14/91						
sheet index	revision	sheet										