



FRA1601G THRU FRA1607G

16.0 AMPS. Glass Passivated Fast Recovery Rectifiers



Voltage Range
50 to 1000 Volts
Current
16.0 Amperes


TO-220A

Features

- ✧ Low forward voltage drop
- ✧ High current capability
- ✧ High reliability
- ✧ High surge current capability

Mechanical Data

- ✧ Cases: Molded plastic
- ✧ Epoxy: UL 94V-0 rate flame retardant
- ✧ Terminals: Leads solderable per MIL-STD-202, Method 208 guaranteed
- ✧ Polarity: As marked
- ✧ High temperature soldering guaranteed: 5.250°C/10 seconds .16", (4.06mm) from case.
- ✧ Mounting position: Any
- ✧ Weight: 2.24 grams



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	FRA 1601G	FRA 1602G	FRA 1603G	FRA 1604G	FRA 1605G	FRA 1606G	FRA 1607G	Units
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current See Fig. 2	16.0							A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	250							A
Maximum Instantaneous Forward Voltage @ 16.0A	1.3							V
Maximum DC Reverse Current @ T _C =25°C at Rated DC Blocking Voltage @ T _C =125°C	5.0 100							uA uA
Maximum Reverse Recovery Time (Note 1)	150				250	500		nS
Typical Thermal resistance RθJC (Note 2)	2.5							°C/W
Operating and Storage Temperature Range T _J , T _{STG}	-65 to +150							°C

Note: 1. Reverse Recovery Test Conditions: I_F=0.5A, I_R=1.0A, I_{RR}=0.25A

2. Thermal Resistance from Junction to Case Mounted on Heatsink.

RATINGS AND CHARACTERISTIC CURVES (FRA1601G THRU FRA1607G)

FIG.1- REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM




FIG.2- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.3- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.4- TYPICAL JUNCTION CAPACITANCE




FIG.5- TYPICAL REVERSE CHARACTERISTICS




FIG.6- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS

