






P/N	DIM.B
10118067-XXX6XXLF	3.43



RECOMMENDED PCB LAYOUT


RECOMMENDED PCB THICKNESS: 1.6mm
TOLERANCE:±0.05mm (TOP VIEW)




mat'l. code				surface	tolerance	projection	product family	
ltr	ecn no	dr	date	ASME Y14.5 tolerances unless otherwise specified	ASME Y14.5		GANGED MJACK	
A	-	WL	11/04/11	0.01	X.X±0.25	 MM [INCH] scale		
B	ELX-N-009383	A.ZH	01/05/12	0.01	X.XX±0.13			
C	ELX-N-13970	Hengj	01/23/13	0.01	X.XXX±0.05			
				dr	WENDY CHEN	05/11/11	dwg no	
				engr	WENDY CHEN	05/11/11		sheet 1 of 2
				chr	WENDY CHEN	05/11/11		
				appd	GARY HSIEH	05/11/11	A4	
sheet	revision	ECN	1	1				type
index	sheet	1	2					

NOTE:


- 1. MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94V-0
COLOR: BLACK.
CONTACTS: COPPER ALLOY.
SHIELD: COPPER ALLOY.
LED SOLDER TAIL: STEEL.
- 2. FINISH:
CONTACTS: 50u" MIN. NICKEL UNDER PLATED OVER ALL.
SELECTIVE GOLD PLATED ON CONTACT AREA,
1u" GOLD PLATED ON SOLDER TAIL.
LED SOLDER TAIL: 100u" MIN. BRIGHT TIN OVER
50u" NICKEL UNDER PLATED.
SHIELD: 20u" MIN. NICKEL OVER ALL.
- 3. LASER MARK FCI LOGO ON THE TOP OF SHIELD.
- 4. "DATE CODE" DESCRIPTION:
XX XX
WEEK
YEAR (EX. : 10--2010)
- 5. PRODUCT PERFORMANCE PER SPEC. : GS-12-0990.
- 6. PACKING SPEC. : GS-14-2170.
- 7. THIS PRODUCT MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED
IN GS-22-008.
- 8. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.




APPEARANCE VIEW




10118067-XX0XXXXLF
(WITHOUT PANEL GROUND)



10118067-XX3XXXXLF
(3 SIDES PANEL GROUND)




10118067-X00XXXXLF
(WITHOUT PANEL GROUND)



10118067-X03XXXXLF
(3 SIDES PANEL GROUND)

9. PART NUMBER DESCRIPTION:



mat'l. code			surface	tolerance	projection	product family	GANGED MJACK	
litr	ecn	no dr	date	ASME Y14.5	ASME Y14.5	title		
C				ASME Y14.5	ASME Y14.5	CAT 3 MULTI-PORTS TAB UP 1x4 WITH SHIELD, W/LED		
				angles	tolerances unless otherwise specified			
				X±1°	X.XX±0.25			
				dr	WENDY CHEN 05/11/11			
				engr	WENDY CHEN 05/11/11			
				chr	WENDY CHEN 05/11/11			
				appl	GARY HSEH 05/11/11			
sheet	revision					dwg no	sheet 2 of 2	size
index	sheet					type	10118067	A4
						CUSTOMER Drawing		